

VOLTAGE RANGE 1000 Volts
CURRENT 2.0 Ampere

FEATURES

- ◆ Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- ◆ Low profile surface mounted package
- ◆ Built-instrain relief
- ◆ Fast switching for high efficiency
- ◆ Glass passivated chip junction
- ◆ High temperature soldering: 250°C/10 secondsat terminals

DO-214AA (SMB)



MECHANICAL DATA

- ◆ Case: JEDED DO-214AA molded plastic over glass passivated chip
- ◆ Terminals: Solder plated, Solderable per MIL-STD-759, method 2026
- ◆ Polarity:Color band denotes cathode end
- ◆ Weight: 0.002 ounce,0.064 gram

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

(Ratings at 25°C ambient temperature unless otherwise specified.)

MAXIMUM RATINGS & THERMAL CHARACTERISTICS

PARAMETERS	SYMBOLS	RS2M-13-F-CN	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	1000	Volts
Maximum RMS Voltage	V_{RMS}	700	Volts
Maximum DC Blocking Voltage	V_{DC}	1000	Volts
Maximum Average Forward Rectified Current at $T_L=100^{\circ}C$	$I_{F(AV)}$	2.0	Amps
Peak Forward Surge Current 8.3ms single half sine wave super imposed on rated load (JEDEC method) $T_L=100^{\circ}C$	I_{FSM}	50	Amps
Typical Thermal Resistance (NOTE1)	$R_{\theta JA}$	55	$^{\circ}C/W$
	$R_{\theta JL}$	18	
Operating and Storage Temperature Range	T_J, T_{STG}	-55 to + 150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS

PARAMETERS	SYMBOLS	RS2M-13-F-CN	UNIT
Maximum Instantaneous Forward Voltageat 2.0A	V_F	1.30	Volts
Maximum DC Reverse Current at rated DC Blocking Voltage	I_R	5.0	μA
		200	
Typical Reverse Recovery Time $I_F=0.5A, I_R=1.0A, I_{RR}=0.25A$	T_{rr}	500	ns
Typical junction capacitance at 4.0V,1MHz	C_J	30	pF

Notes:

- 1.Thermal resistance from Junction to ambient and from junction to lead mounted on P.C.B. with $0.27 \times 0.27"$ (7.0 × 7.0mm) copper pad areas.

RATINGS AND CHARACTERISTIC CURVES

FIG. 1 - FORWARD CURRENT DERATING CURVE




FIG. 2 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 3 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 4 - TYPICAL REVERSE CHARACTERISTICS





FIG. 5 - TYPICAL JUNCTION CAPACITANCE



NOTICE

The information presented in this document is for reference only. Involving product optimization and productivity improvement, ChipNobo reserves the right to adjust product indicators and upgrade some technical parameters. ChipNobo is entitled to be exempted from liability for any delay or non-delivery of the information disclosure process that occurs.

本文件中提供的信息仅供参考。涉及产品优化和生产效率改善，ChipNobo 有权调整产品指标和部分技术参数的升级，所出现信息披露过程存在延后或者不能送达的情形，ChipNobo 有获免责权。

The product listed herein is designed to be used with residential and commercial equipment, and do not support sensitive items and specialized equipment in areas where sanctions do exist. ChipNobo Co., Ltd or anyone on its behalf, assumes no responsibility or liability for any damages resulting from improper use.

此处列出的产品旨在民用和商业设备上使用，不支持确有制裁地区的敏感项目和特殊设备，ChipNobo 有限公司或其代表，对因不当使用而造成的任何损害不承担任何责任。

For additional information, please visit our website <http://www.chipnobo.com>, or consult your nearest Chipnobo sales office for further assistance.

欲了解更多信息，请访问我们的网站 <http://www.chipnobo.com>，或咨询离您最近的 Chipnobo 销售办事处以获得进一步帮助。