



MICRO SWITCH
FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED MFG CODE 91929

SWITCH-TOGGLE




CATALOG LISTING
1TL156 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN		
	KEYWAY SIDE (1-2)	CENTER (1-2)	OPPOSITE KEYWAY (2-3)
ITL156-1	ON	OFF	ON
ITL156-2	OFF	NONE	ON
⊙	ON	NONE	ON
ITL156-21	NONE	OFF	ON
ITL156-31	NONE	ON	ON
ITL156-4	MOM OFF	NONE	ON
ITL156-5	MOM ON	OFF	ON
ITL156-6	MOM ON	NONE	OFF
ITL156-7	MOM ON	OFF	MOM ON
ITL156-8	MOM ON	NONE	ON
ITL156-51	NONE	ON	MOM ON
ITL156-61	MOM ON	OFF	NONE

MILITARY RATING (AMPS)							
RESISTIVE LOAD				LAMP LOAD		INDUCTIVE LOAD	
DC VOLTS		AC VOLTS					
28	125	250	125	250	28 VDC	125 VAC	125 VAC
20	.75	.5	15	6	5	3	15 10
(REFER TO L191 FOR UL RATING)							
15	.75	.5	15	6	4	2	10 7
(REFER TO L192 FOR UL RATING)							



- NOTES
- SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
- 3 FURNISHED UNASSEMBLED
- 4 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS

SCALE FULL
DO NOT SCALE PRINT
UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (0) .030
TWO PLACE (.00) .018
THREE PLACE (.000) .008
ANGLES .008
WEIGHT .07 LBS APPROX

15A-125,250 OR 277VAC
1/2HP-125VAC;1HP-250,277VAC
5A-125VAC "L" CODE L191


10A-125,250 OR 277VAC
1/4HP-125VAC;1/2HP-250,277VAC
3A-125VAC "L" CODE L192

MICRO SWITCH
FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED MFG CODE 91929

SWITCH-TOGGLE




CATALOG LISTING
1TL156 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN		
	KEYWAY SIDE (1-2)	CENTER (1-2)	OPPOSITE KEYWAY (2-3)
ITL156-1	ON	OFF	ON
ITL156-2	OFF	NONE	ON
ITL156-3	ON	NONE	ON
ITL156-21	NONE	OFF	ON
ITL156-31	NONE	ON	ON
ITL156-4	MOM OFF	NONE	ON
ITL156-5	MOM ON	OFF	ON
ITL156-6	MOM ON	NONE	OFF
ITL156-7	MOM ON	OFF	MOM ON
ITL156-8	MOM ON	NONE	ON
ITL156-51	NONE	ON	MOM ON
ITL156-61	MOM ON	OFF	NONE

MILITARY RATING (AMPS)							
RESISTIVE LOAD DC VOLTS				LAMP LOAD 125 VAC		INDUCTIVE LOAD 125 VAC	
28	125	250	125	250	28	125	28
20	.75	.5	15	6	5	3	15
(REFER TO L191 FOR UL RATING)							
15	.75	.5	15	6	4	2	10
(REFER TO L192 FOR UL RATING)							



NOTES

- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
- 2 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
- 3 FURNISHED UNASSEMBLED

4 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS

SCALE FULL
DO NOT SCALE PRINT
UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (0) .030
TWO PLACE (.00) .018
THREE PLACE (.000) .008
ANGLES .008
WEIGHT .07 LBS APPROX

15A-125, 250 OR 277VAC
1/2HP-125VAC; 1HP-250, 277VAC
5A-125VAC "L" CODE L191
10A-125, 250 OR 277VAC
1/4HP-125VAC; 1/2HP-250, 277VAC
3A-125VAC "L" CODE L192