




Cable Assemblies > Data Bus Components > Data Bus Connectors



Connector Type: **Plug**
Connector Style: **Bayonet**
Polarization (Bayonet Style): **A**

Features

Product Type Features

Product Type	Data Bus Component
Connector Type	Plug
Connector Style	Bayonet

Termination Features

Connection Type	Solder
-----------------	--------

Mechanical Attachment

Polarization (Bayonet Style)	A
------------------------------	---

Usage Conditions

Operating Temperature (Max)	125 °C
-----------------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 750984-004
[10612-24-9](#)

Customers Also Bought



TE Part #3-1617028-1
[HFW1105D00 = HFW 1/2 SIZE RELA](#)



TE Part #808535S002
[202D263-4-120-CS2542](#)



TE Part #808959-000
[203M222-19C16](#)

TE Part #202057-000
[204M010-19B08-12](#)



TE Part #680111-000
[D-150-21](#)


TE Part #106556-000
[D-621-0653](#)



TE Part #348579-000
[LNCL-14-355-GK](#)



TE Part #1-1393139-9
[MDR-170-2=MDR](#)



TE Part #0657620002
[S03-02-RCS405](#)



TE Part #740072N002
[SO63-3-01CS2720](#)

Documents

Product Drawings

[DK-621-0433](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_524907-000_O.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_524907-000_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_524907-000_O.3d_stp.zip](#)

English

Datasheets & Catalog Pages

[Data Bus Components Brochure](#)

English

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[REACH Substance Communication Document](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English