



APPLICABLE WIRE GRIP SIZE IDENTIFICATION

(5/1)




7116-4270-02

(5/1)




7116-4271-02

(5/1)







7116-4272-02

(5/1)




△7196-2077-02




2 NOTES:


1. PARTS MUST BE PURCHASED FROM YAZAKI.
2. PARTS MUST BE FREE OF BURRS AND SHARP EDGES THAT MAY BE DETRIMENTAL TO SATISFACTORY ASSEMBLY, SAFE HANDLING OR FUNCTION OF THE PART.
3. MATERIAL: COPPER ALLOY.
4. PLATING: TIN (Sn) PLATED.
5. MATING PART NUMBER: SEE 7114-4110-02:R DRAWING.
6. PART TO COMPLY WITH YPES-31-038 REQUIREMENTS
7. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.



SECTION A-A



SECTION B-B



ISSUE MARK

	03-22-2021	REDRAWN, ADDED WIRE SIZE & REVISED NOTES	C21-A253	M.S
	05-27-2004	CHANGED NAME, ETC.	C04-Z511	Y.W
-	07-17-2001	NEW	C01-X670	T.N
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE											
	10MAX	50MAX	100MAX	250MAX	250OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCEN
A	±0.15	±0.20	±0.30	±0.50	±0.75					±3°	0.1
B	±0.20	±0.30	±0.55	±0.95	±1.40	±0.20	±0.30	±0.50	±2.50	±3°	0.1
(C)	±0.30	±0.50	±0.80	±1.40	±2.00					±3°	0.15
SPECIFIED										MASS	SEE TABLE

CUSTOMER							MATL. SPEC.		SEE NOTES		TREAT. & FIN.		SEE NOTES	
CUSTOMER PART NO.							CUSTOMER DWG NO.							
OFFICE YNA							TRIAL PART NO.							
VENDOR							NAME							
VENDOR NO.							UNSEALED FEMALE TERMINAL							
DWG TYPE		DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE	PART NO.					
R		7116-4270-02.M		07-10-2001		mm	10/1	3	CH. CODE 7116-4270-02, ETC.					
APPROVED		CHECKED		CHECKED		DESIGN		DRAWN		DWG NO. 7116-4270-02:R				
						NAGANO		MICHELLE SANTILLAN		YAZAKI CORPORATION				
						10-02-2000		04-13-2021						