





REV. 0

DCO 17683

COIL: @ 25°C	
RESISTANCE	310 OHMS ±10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	5.6 VDC
MUST RELEASE	3.35 VDC MAX. 0.55 VDC MIN

ENVIRONMENT:	
VIBRATION	10 Hz TO 2500 Hz @ 20 g's
SHOCK	50 g's 11 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	
OPERATE 6 MS MAX	
RELEASE 5 MS MAX	
CONTACT BOUNCE 2 MS MAX	

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	2 AMPS 28 VDC
	0.1 AMP 115 VAC RESISTIVE 0.5 AMPS
	28 VDC INDUCTIVE 100,000 OPERATIONS

DR. B.D. 02JUL03 CK. *WBS 7/24/03*

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/44-026L REV.

"HMS" RELAY

HMS1201S110L