


Features 特点

Low Dropout Voltage 低落差电压

1.Vss/Adj 2.Vo 3.Vi

SOT-89



Application 应用

PC Motherboard 主板

LCD Monitor 液晶屏

Graphic Card 显卡

Modem 调制解调器

Printer 打印机

Absolute Maximum Ratings 最大额定值


($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	Rat 额定值	Unit 单位
Input Voltage 输入电压	V_i	15	V
Operating Current 工作电流	I_o	1000	mA
Thermal Resistance Junction-Ambient 热阻	$R_{\theta JA}$	250	$^{\circ}\text{C}/\text{W}$
Solder Temperature 焊接温度	T_d	260	$^{\circ}\text{C}$
Solder Time 焊接时间	T_d	10	S
Operating Ambient Temperature 工作温度	T_A	+85	$^{\circ}\text{C}$
Junction and Storage Temperature 结温和储藏温度	T_J, T_{stg}	-40to+125 $^{\circ}\text{C}$	

Electrical Characteristics 电特性

 ($V_{IN} \leq 10V$ $T_J = 25^\circ C$ unless otherwise noted 如无特殊说明)

Characteristic 特性参数	Symbol 符号	Part No. 料号	Test Condition 测试条件	Min 最小值	Type 典型值	Max 最大值	Unit 单位
Output Voltage 输出电压	V_O	AZ1117CR -3.3TRG1-CN	$I_O = 10mA$ $V_I = 5.3$	3.251	3.3	3.350	V
			$10mA \leq I_O \leq 0.8A$ $4.8 \leq V_I \leq 12$	3.234	3.3	3.366	
Line Regulation 线性调整率	LNR	AZ1117CR -3.3TRG1-CN	$I_O = 10mA$ $1.5 \leq V_I - V_O \leq 8.7$		1	7	mV
Load Regulation 负载调整率	LDR	AZ1117CR -3.3TRG1-CN	$10mA \leq I_O \leq 0.8A$ $V_I - V_O = 1.5$			13.2	mV
Dropout Voltage	V_D	落差电压	$\Delta V_R = 1\%$ $I_O = 0.8A$		1.2	1.3	V
Adjust Pin Current	I_{adj}	电流调整	$I_O = 10mA$			120	μA
Adjust Current Change	ΔI_{adj}	电流调整率	$1.5 \leq V_I - V_O \leq 12$ $I_O = 10mA$			5	μA
Min Load Current	I_L	负载电流	$V_I = 5V$ $V_{adj} = 0V$			7	mA
Quiescent Current	I_q	静态电流	$V_I = V_O + 1.25$		2	5	mA
Temperature Stability 温度稳定性					0.5		%
Long Term Stability 长期稳定性			$T_A = 125^\circ C$ 1000hrs		0.3		%
RMS Output Noise(% of V_{out})输出噪声			$T_A = 125^\circ C$		0.003		%
Thermal Shutdown Hysteresis 热特性					25		$^\circ C$

SOT-89 Dimension 外形封装尺寸


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.40	1.60	0.055	0.063
B	0.40	0.56	0.016	0.022
B1	0.35	0.48	0.014	0.019
C	0.35	0.44	0.014	0.017
D	4.40	4.60	0.173	0.181
D1	1.35	1.83	0.053	0.072
e	1.45	1.55	0.057	0.061
e1	2.95	3.05	0.116	0.120
E	2.29	2.60	0.090	0.102
H	3.75	4.25	0.148	0.167
L	0.80	1.20	0.031	0.047

NOTICE

The information presented in this document is for reference only. Involving product optimization and productivity improvement, ChipNobo reserves the right to adjust product indicators and upgrade some technical parameters. ChipNobo is entitled to be exempted from liability for any delay or non-delivery of the information disclosure process that occurs.

本文件中提供的信息仅供参考。涉及产品优化和生产效率改善，ChipNobo 有权调整产品指标和部分技术参数的升级，所出现信息披露过程存在延后或者不能送达的情形，ChipNobo 有获免责权。

The product listed herein is designed to be used with residential and commercial equipment, and do not support sensitive items and specialized equipment in areas where sanctions do exist. ChipNobo Co., Ltd or anyone on its behalf, assumes no responsibility or liability for any damages resulting from improper use.

此处列出的产品旨在民用和商业设备上使用，不支持确有制裁地区的敏感项目和特殊设备，ChipNobo 有限公司或其代表，对因不当使用而造成的任何损害不承担任何责任。

For additional information, please visit our website <http://www.chipnobo.com>, or consult your nearest Chipnobo sales office for further assistance.

欲了解更多信息，请访问我们的网站 <http://www.chipnobo.com>，或咨询离您最近的 Chipnobo 销售办事处以获得进一步帮助。