


### SOD-123



### 特征 Features

- 齐纳击穿阻抗低; Low Zener Impedance
- 最大功率耗散 500mW; Power Dissipation of 500mW
- 高稳定性和可靠性。High Stability and High Reliability

### 机械数据 Mechanical Data

- 封装: SOD-123 封装 SOD-123 Small Outline Plastic Package
- 极性: 色环端为负极 Polarity: Color band denotes cathode end
- 环氧树脂UL 易燃等级 Epoxy UL: 94V-0
- 安装位置: 任意 Mounting Position: Any

极限值和温度特性(TA = 25℃ 除非另有规定)

**Maximum Ratings & Thermal Characteristics** (Ratings at 25℃ ambient temperature unless otherwise specified.)

| 参数 Parameters                                  | 符号 Symbol | 数值 Value          | 单位 Unit           |
|------------------------------------------------|-----------|-------------------|-------------------|
| 功率消耗 Power Dissipation                         | Pd        | 500 <sup>1)</sup> | mW                |
| 正向压降 Forward Voltage @IF=10mA                  | Vf        | 0.9 <sup>2)</sup> | V                 |
| 存储温度 Storage temperature range                 | Ts        | -65-+150          | ℃                 |
| 工作结温 Junction/Operating Temperature            | Tj        | 150               | ℃                 |
| 热阻 Thermal Resistance from Junction to Ambient | RthA      | 400               | K/W <sup>1)</sup> |

1) Device mounted on ceramic PCB: 7.6mm x 9.4mm x 0.87mm with pad areas 25mm<sup>2</sup>

2) Short duration test pulse used to minimize self-heating effect



电特性 (TA = 25℃ 除非另有规定)

**Electrical Characteristics** (Ratings at 25℃ ambient temperature unless otherwise specified.)


| Device    | Marking | Zener Voltage Range |        |        |     | Maximum Zener Impedance <sup>3)</sup> |          |     | Maximum Reverse Current |     | Typical Temperature coefficient @ IZTC=mV/°C |     | Test Current IZTC |
|-----------|---------|---------------------|--------|--------|-----|---------------------------------------|----------|-----|-------------------------|-----|----------------------------------------------|-----|-------------------|
|           |         | Vz@Izt              |        |        | Izt | Zzt @Izt                              | Zzk @Izk | Izk | IR                      | VR  | Min                                          | Max |                   |
|           |         | Nom(V)              | Min(V) | Max(V) | mA  | Ω                                     |          | mA  | uA                      | V   |                                              |     |                   |
| BZT52C2V0 | WY      | 2.0                 | 1.80   | 2.15   | 5   | 150                                   | 600      | 1.0 | 100                     | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C2V4 | WX      | 2.4                 | 2.2    | 2.6    | 5   | 100                                   | 600      | 1.0 | 50                      | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C2V7 | W1      | 2.7                 | 2.5    | 2.9    | 5   | 100                                   | 600      | 1.0 | 20                      | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C3V0 | W2      | 3.0                 | 2.8    | 3.2    | 5   | 95                                    | 600      | 1.0 | 10                      | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C3V3 | W3      | 3.3                 | 3.1    | 3.5    | 5   | 95                                    | 600      | 1.0 | 5                       | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C3V6 | W4      | 3.6                 | 3.4    | 3.8    | 5   | 90                                    | 600      | 1.0 | 5                       | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C3V9 | W5      | 3.9                 | 3.7    | 4.1    | 5   | 90                                    | 600      | 1.0 | 3                       | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C4V3 | W6      | 4.3                 | 4.0    | 4.6    | 5   | 90                                    | 600      | 1.0 | 3                       | 1.0 | -3.5                                         | 0   | 5                 |
| BZT52C4V7 | W7      | 4.7                 | 4.4    | 5.0    | 5   | 80                                    | 500      | 1.0 | 3                       | 2.0 | -3.5                                         | 0.2 | 5                 |
| BZT52C5V1 | W8      | 5.1                 | 4.8    | 5.4    | 5   | 60                                    | 480      | 1.0 | 2                       | 2.0 | -2.7                                         | 1.2 | 5                 |
| BZT52C5V6 | W9      | 5.6                 | 5.2    | 6.0    | 5   | 40                                    | 400      | 1.0 | 1                       | 2.0 | -2.0                                         | 2.5 | 5                 |
| BZT52C6V2 | WA      | 6.2                 | 5.8    | 6.6    | 5   | 10                                    | 150      | 1.0 | 3                       | 4.0 | 0.4                                          | 3.7 | 5                 |
| BZT52C6V8 | WB      | 6.8                 | 6.4    | 7.2    | 5   | 15                                    | 80       | 1.0 | 2                       | 4.0 | 1.2                                          | 4.5 | 5                 |
| BZT52C7V5 | WC      | 7.5                 | 7.0    | 7.9    | 5   | 15                                    | 80       | 1.0 | 1                       | 5.0 | 2.5                                          | 5.3 | 5                 |
| BZT52C8V2 | WD      | 8.2                 | 7.7    | 8.7    | 5   | 15                                    | 80       | 1.0 | 0.7                     | 5.0 | 3.2                                          | 6.2 | 5                 |
| BZT52C9V1 | WE      | 9.1                 | 8.5    | 9.6    | 5   | 15                                    | 100      | 1.0 | 0.5                     | 6.0 | 3.8                                          | 7.0 | 5                 |
| BZT52C10  | WF      | 10                  | 9.4    | 10.6   | 5   | 20                                    | 150      | 1.0 | 0.2                     | 7.0 | 4.5                                          | 8.0 | 5                 |

| Device   | Marking | Zener Voltage Range |        |        |     | Maximum Zener Impedance |          |     | Maximum Reverse Current |      | Typical Temperature coefficient @ IZTC=mV/°C |      | Test Current IZTC |
|----------|---------|---------------------|--------|--------|-----|-------------------------|----------|-----|-------------------------|------|----------------------------------------------|------|-------------------|
|          |         | Vz@Izt              |        |        | Izt | Zzt @Izt                | Zzk @Izk | Izk | IR                      | VR   | Min                                          | Max  |                   |
|          |         | Nom(V)              | Min(V) | Max(V) | mA  | Ω                       |          | mA  | uA                      | V    |                                              |      |                   |
| BZT52C11 | WG      | 11                  | 10.4   | 11.6   | 5   | 20                      | 150      | 1.0 | 0.1                     | 8.0  | 5.4                                          | 9.0  | 5                 |
| BZT52C12 | WH      | 12                  | 11.4   | 12.7   | 5   | 25                      | 150      | 1.0 | 0.1                     | 8.0  | 6.0                                          | 10.0 | 5                 |
| BZT52C13 | WI      | 13                  | 12.4   | 14.1   | 5   | 30                      | 170      | 1.0 | 0.1                     | 8.0  | 7.0                                          | 11.0 | 5                 |
| BZT52C15 | WJ      | 15                  | 13.8   | 15.6   | 5   | 30                      | 200      | 1.0 | 0.1                     | 10.5 | 9.2                                          | 13.0 | 5                 |
| BZT52C16 | WK      | 16                  | 15.3   | 17.1   | 5   | 40                      | 200      | 1.0 | 0.1                     | 11.2 | 10.4                                         | 14.0 | 5                 |
| BZT52C18 | WL      | 18                  | 16.8   | 19.1   | 5   | 45                      | 225      | 1.0 | 0.1                     | 12.6 | 12.4                                         | 16.0 | 5                 |
| BZT52C20 | WM      | 20                  | 18.8   | 21.2   | 5   | 55                      | 225      | 1.0 | 0.1                     | 14.0 | 14.4                                         | 18.0 | 5                 |
| BZT52C22 | WN      | 22                  | 20.8   | 23.3   | 5   | 55                      | 250      | 1.0 | 0.1                     | 15.4 | 16.4                                         | 20.0 | 5                 |
| BZT52C24 | WO      | 24                  | 22.8   | 25.6   | 5   | 70                      | 250      | 1.0 | 0.1                     | 16.8 | 18.4                                         | 22.0 | 5                 |
| BZT52C27 | WP      | 27                  | 25.1   | 28.9   | 2   | 80                      | 300      | 0.5 | 0.1                     | 18.9 | 21.4                                         | 25.3 | 2                 |
| BZT52C30 | WQ      | 30                  | 28.0   | 32.0   | 2   | 80                      | 300      | 0.5 | 0.1                     | 21.0 | 24.4                                         | 29.4 | 2                 |
| BZT52C33 | WR      | 33                  | 31.0   | 35.0   | 2   | 80                      | 325      | 0.5 | 0.1                     | 23.1 | 27.4                                         | 33.4 | 2                 |
| BZT52C36 | WS      | 36                  | 34.0   | 38.0   | 2   | 90                      | 350      | 0.5 | 0.1                     | 25.2 | 30.4                                         | 37.4 | 2                 |
| BZT52C39 | WT      | 39                  | 37.0   | 41.0   | 2   | 130                     | 350      | 0.5 | 0.1                     | 27.3 | 33.4                                         | 41.2 | 2                 |
| BZT52C43 | WU      | 43                  | 40.0   | 46.0   | 2   | 100                     | 700      | 1.0 | 0.1                     | 32.0 | 10.0                                         | 12.0 | 5                 |
| BZT52C47 | WV      | 47                  | 44.0   | 50.0   | 2   | 100                     | 750      | 1.0 | 0.1                     | 35.0 | 10.0                                         | 12.0 | 5                 |
| BZT52C51 | WW      | 51                  | 48.0   | 54.0   | 2   | 125                     | 750      | 1.0 | 0.1                     | 38.0 | 10.0                                         | 12.0 | 5                 |
| BZT52C56 | XW      | 56                  | 52.0   | 60.0   | 2   | 135                     | 700      | 1.0 | 0.1                     | 39.0 | 10.0                                         | 12.0 | 5                 |
| BZT52C62 | 6E      | 62                  | 58.0   | 66.0   | 2   | 200                     | 1000     | 1.0 | 0.2                     | 47.0 | 10.0                                         | 12.0 | 5                 |
| BZT52C68 | 6F      | 68                  | 64.0   | 72.0   | 2   | 250                     | 1000     | 1.0 | 0.2                     | 52.0 | 10.0                                         | 12.0 | 5                 |
| BZT52C75 | 6H      | 75                  | 70.0   | 79.0   | 2   | 300                     | 1000     | 1.0 | 0.2                     | 57   | 10.0                                         | 12.0 | 5                 |


**Breakdown characteristics**  
at Tj=constant (pulsed)




Forward characteristics




Admissible power dissipation versus ambient temperature




Pulse thermal resistance versus pulse duration




Dynamic resistance versus Zener current




Capacitance versus Zener voltage




Dynamic resistance versus Zener current




Dynamic resistance versus Zener current




Thermal differential resistance versus Zener voltage




Dynamic resistance versus Zener voltage




Temperature dependence of Zener voltage versus Zener voltage




Temperature dependence of Zener voltage versus Zener voltage




Change of Zener voltage versus junction temperature




Change of Zener voltage versus junction temperature



Change of Zener voltage from turn-on up to the point of thermalequilibrium versus Zener voltage



### SOD-123 PACKAGE OUTLINE Plastic surface mounted package




| SYMBOL | DIMENSIONS |       |
|--------|------------|-------|
|        | MIN.       | MAX.  |
| A      | 1.050      | 1.250 |
| A1     | 0.000      | 0.100 |
| A2     | 1.050      | 1.150 |
| b      | 0.450      | 0.650 |
| c      | 0.080      | 0.150 |
| D      | 1.500      | 1.700 |
| E      | 2.600      | 2.800 |
| E1     | 3.550      | 3.850 |
| L      | 0.500REF   |       |
| L1     | 0.250      | 0.450 |
| θ      | 0°         | 8°    |

### 焊盘设计参考

Precautions: PCB Design

Recommended land dimensions for SOD-123 diode. Electrode patterns for PCBs



中心距: 3.24  
脚宽: 0.55  
焊盘宽: 1.00  
脚长: 0.50  
焊盘长: 0.80

### 技术要求:

- 1, 塑封体尺寸: 2.70 X 1.60
- 2: 未注公差为:  $\pm 0.05$
- 3, 所有单位: mm

**NOTICE**

The information presented in this document is for reference only. Involving product optimization and productivity improvement, ChipNobo reserves the right to adjust product indicators and upgrade some technical parameters. ChipNobo is entitled to be exempted from liability for any delay or non-delivery of the information disclosure process that occurs.

本文件中提供的信息仅供参考。涉及产品优化和生产效率改善，ChipNobo 有权调整产品指标和部分技术参数的升级，所出现信息披露过程存在延后或者不能送达的情形，ChipNobo 有获免责权。

The product listed herein is designed to be used with residential and commercial equipment, and do not support sensitive items and specialized equipment in areas where sanctions do exist. ChipNobo Co., Ltd or anyone on its behalf, assumes no responsibility or liability for any damages resulting from improper use.

此处列出的产品旨在民用和商业设备上使用，不支持确有制裁地区的敏感项目和特殊设备，ChipNobo 有限公司或其代表，对因不当使用而造成的任何损害不承担任何责任。

For additional information, please visit our website <http://www.chipnobo.com>, or consult your nearest Chipnobo sales office for further assistance.

欲了解更多信息，请访问我们的网站 <http://www.chipnobo.com>，或咨询离您最近的 Chipnobo 销售办事处以获得进一步帮助。