

1.Features

- $V_{DS(V)}=60V$
- $I_D=3A$
- $R_{DS(ON)}<80m\Omega(V_{GS}=10V)$
- $R_{DS(ON)}<95m\Omega(V_{GS}=4.5V)$



2.Applications

- Load/Power Switching
- Interfacing Switching
- Logic Level Shift
- Battery Management for Ultra Small Portable

3.Pinning information

Pin	Symbol	Description
1	G	GATE
2	S	SOURCE
3	D	DRAIN

SOT-23



4.Absolute Maximum Ratings $T_A=25^{\circ}C$

Parameter		Symbol	Value	Units
Drain-Source Voltage		V_{DS}	60	V
Gate-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current	$T_A=25^{\circ}C$	I_D	3	A
	$T_A=70^{\circ}C$		2.3	
Pulsed Drain Current *		I_{DM}	10	
Power Dissipation	$T_A=25^{\circ}C$	P_D	1.38	W
Linear Derating Factor			0.01	W/ $^{\circ}C$
Thermal Resistance.Junction-to-ambient		R_{thJa}	90	$^{\circ}C/W$
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 150	$^{\circ}C$

*2.Pulse width $\leq 300\mu s$,duty cycle $\leq 2\%$.









5. Electrical Characteristics $T_A = 25^\circ\text{C}$

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-Source Breakdown Voltage	V_{DSS}	$I_D = 250\mu\text{A}$, $V_{GS} = 0\text{V}$	60			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 60\text{V}$, $V_{GS} = 0\text{V}$			10	μA
		$V_{DS} = 48\text{V}$, $V_{GS} = 0\text{V}$, $T_J = 70^\circ\text{C}$			25	
Gate-Body leakage current	I_{GSS}	$V_{DS} = 0\text{V}$, $V_{GS} = \pm 20\text{V}$			± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = -250\mu\text{A}$	1		3	V
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS} = 10\text{V}$, $I_D = 3\text{A}$			80	m Ω
		$V_{GS} = 4.5\text{V}$, $I_D = 2\text{A}$			95	
Forward Transconductance	g_{FS}	$V_{DS} = 5\text{V}$, $I_D = 3\text{A}$		5		S
Input Capacitance	C_{iss}	$V_{GS} = 0\text{V}$, $V_{DS} = 25\text{V}$, $f = 1\text{MHz}$		490	780	pF
Output Capacitance	C_{oss}			55		
Reverse Transfer Capacitance	C_{rss}			40		
Total Gate Charge	Q_g	$V_{DS} = 48\text{V}$		6	10	nC
Gate Source Charge	Q_{gs}	$V_{GS} = 4.5\text{V}$		1.6		
Gate Drain Charge	Q_{gd}	$I_D = 3\text{A}$		3		
Turn-On DelayTime	$t_{D(on)}$	$V_{GS} = 10\text{V}$, $V_{DS} = 30\text{V}$ $R_D = 30\Omega$, $R_{GEN} = 3.3\Omega$ $I_D = 1\text{A}$		6		ns
Turn-On Rise Time	t_r			5		
Turn-Off DelayTime	$t_{D(off)}$			16		
Turn-Off Fall Time	t_f			3		
Body Diode Reverse Recovery Time	t_{rr}	$I_S = 3\text{A}$, $di/dt = 100\text{A}/\mu\text{s}$		25		
Body Diode Reverse Recovery Charge	Q_{rr}	$I_S = 3\text{A}$, $di/dt = 100\text{A}/\mu\text{s}$		26		nC
Diode Forward Voltage	V_{SD}	$I_S = 1.2\text{A}$, $V_{GS} = 0\text{V}$			1.2	V







6.1Typical Characteristics

 I_D-Drain Current (A) $T_A = 25^{\circ}\text{C}$ $V_G = 3.0\text{V}$ V_{DS} - Drain-to-Source Voltage (V)	 I_D-Drain Current (A) $T_A = 150^{\circ}\text{C}$ $V_G = 3.0\text{V}$ V_{DS} - Drain-to-Source Voltage (V)
Fig 1. Typical Output Characteristics	Fig 2. Typical Output Characteristics
 $R_{DS(on)}$ (mΩ) $I_D = 2\text{A}$ $T_A = 25^{\circ}\text{C}$ V_{GS} - Gate-to-Source Voltage (V)	 Normalized $R_{DS(on)}$ $I_D = 3\text{A}$ $V_G = 10\text{V}$ T_J, Junction Temperature ($^{\circ}\text{C}$)
Fig 3. On-Resistance v.s. Gate Voltage	Fig 4. Normalized On-Resistance v.s. Junction Temperature
 I_S (A) $T_J = 150^{\circ}\text{C}$ $T_J = 25^{\circ}\text{C}$ V_{SD}, Source-to-Drain Voltage (V)	 Normalized $V_{GS(th)}$ (V) T_J - Junction Temperature ($^{\circ}\text{C}$)
Fig 5. Forward Characteristic of Reverse Diode	Fig 6. Gate Threshold Voltage v.s. Reverse Diode Junction Temperature




6.2Typical Characterisitics

	
Fig 7. Gate Charge Characteristics	Fig 8. Typical Capacitance Characteristics
	
Fig 9. Maximum Safe Operating Area	Fig 10. Effective Transient Thermal Impedance



7.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	b _p	C	D	E	H _E	A1	L _p
Min	0.95	1.78	0.35	0.08	2.70	1.20	2.20	0.013	0.20
Max	1.40	2.04	0.50	0.19	3.10	1.65	3.00	0.100	0.50



8.Ordering information



ww: Batch Code

Order Code	Package	Base QTY	Delivery Mode
UMW SI2310A	SOT-23	3000	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.