

C. Westerbe 12-2-92
APPROVED/DATE

SAFETY ORGANIZATION(S):

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

- UL 544
- CSA 22.2, NO. 0, 0.4, 8
- VDE 0565-3

OPERATING SPECIFICATIONS:

- LINE VOLTAGE/CURRENT, 15 AMP., 120/250 VAC
- 50-60Hz
- LINE FREQUENCY, 50°C
- MAX. CASE RISE & RATED CURRENT, 2mA @ 120V 60 Hz
- MAX. LEAKAGE CURRENT, EACH LINE TO GROUND, 5µA @ 250V 50 Hz
- OPERATING AMBIENT TEMP. RANGE, -10°C TO +40°C @ RATED CURRENT, I_r
- IN AN AMBIENT, T_a, HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_o, IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{85 - T_a}{45}}$$

RELIABILITY SPECIFICATIONS:

- STORAGE TEMPERATURE, -40°C TO +85°C
- HUMIDITY, 21 DAYS @ 40°C 95% RH
- CURRENT OVERLOAD TEST, 6 TIMES RATED CURRENT FOR 8 SECONDS

TEST SPECIFICATIONS:

- INDUCTANCE, 5.07 mH NOMINAL
- CAPACITANCE, MEASURED @ 1 KHz, 0.25 VAC MAX., 25°C ±1°C
- LINE TO LINE, 2.07µF ±20%
- DISCHARGE RESISTOR, 165 KΩ
- LINE/GROUND AND LINE/LINE, 6000 MΩ (MIN) AT 100 VDC
- INSULATION RESISTANCE, 20°C AND 50% RH
- (W/O DISCHARGE RESISTOR)

RECOMMENDED RECEIVING INSPECTION HIPOT:

- LINE TO GROUND, 2250 VDC FOR 1 MINUTE
- LINE TO LINE, 1450 VDC FOR 1 MINUTE
- FILTER APPROVAL, THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.

TOLERANCE EXCEPT AS NOTED

DECIMAL, .XXX	.XX	.X	ANGLES
ENGLISH, ±.025			± 1°
METRIC, ±			

MATERIAL:

AS SUPPLIED


FINISH:

AS SUPPLIED



POWER LINE FILTER

SCALE	DATE	REV.
NTS	7-21-92	1
DES. BY	CFW	CFW
		15EHT6.01



50Ω - 50Ω (MINIMUM) INSERTION LOSS

FREQUENCY MHz	.01	.03	.05	.07	.1	.15	.3	.5	1	2	5	10	20	30
COMMON dB	4	13	18	21	24	27	35	41	34	22	12	5	2	
DIFF. dB	12	19	15	13	24	51	70	70	70	70	70	70	65	55

This document is proprietary to CORCOM INC. and is not to be reproduced nor used for manufacturing purposes except on CORCOM's order or prior written consent.

