

DFN1006-3L Plastic-Encapsulate ESD Protection Diodes


Features

- Low leakage current
- DFN1006-3L surface mount package
- IEC 61000-4-2 (ESD Air): ±15kV
- IEC 61000-4-2 (ESD Contact): ±20kV
- IEC 61000-4-5 (Lightning 8/20μs): 5A

Applications


- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebook computers
- Portable Instrumentation, Digital Cameras, Peripherals
- Audio Players, Keypads, Side Keys, USB 2.0
- LCD Displays

Function Diagram



Reverse Working Voltage
5V Max.
Ultra Small capacitance
C_{1,2}=0.4pF(Typ.)
C_{1 or 2 to 3}=0.8pF(Typ.)

DFN1006-3L




Maximum Ratings (Ta=25°C Unless otherwise specified)

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
V _{ESD}	Electrostatic Discharge Voltage	ESD per IEC 61000-4-2(Air)	±15	KV
		ESD per IEC 61000-4-2(Contact)	±20	KV
P _{PP}	Peak Pulse Power	tp = 8/20 μs	75	W
I _{PP}	Rated Peak Pulse Current	tp = 8/20 μs	5.0	A
T _J	Operating JunctionTemperature Range	—	-55 to +125	°C
T _{STG}	Operating JunctionTemperature Range	—	-55 to +150	°C

Electrical Parameter





SYMBOL	PARAMETER
V _C	Clamping Voltage @ I _{PP}
V _{BR}	Breakdown Voltage @ I _T
I _{PP}	Peak Pulse Current
I _T	Test Current
I _R	Reverse Leakage Current @ VRWM
V _{RWM}	Peak Reverse Working Voltage
P _{PP}	Peak Pulse Power Dissipation
C _J	Junction Capacitance @ V _R =0V,f=1MHz
I _F	Forward Current
V _F	Forward Voltage @I _F



● Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	CONDITION	Min	Typ	Max	UNIT
Peak Reverse Working Voltage	V_{RWM}	$T_a=25^{\circ}C$	—	—	5.0	V
Breakdown Voltage	V_{BR}	$I_R=1mA, T_a=25^{\circ}C$	6.0	—	9.0	V
Reverse Leakage Current	I_R	$V_R=5V, T_a=25^{\circ}C$	—	—	0.2	μA
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$	—	—	10	V
		$I_{PP}=5A, t_p=8/20\mu s$	—	—	15	
Junction Capacitance	C_J	$V_R=0V, f=1MHz, \text{between pin1 and pin2}$	—	0.4	0.6	pF
		$V_R=0V, f=1MHz, \text{pin1 or pin2 to pin3}$	—	0.8	—	


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ordering Information

PREFERED P/N	PACKAGE	SIZE(mm)	DELIVERY MODE	MPQ(PCS)
H5VU13U	DFN1006-3L	1.00×0.50×0.45	7" REEL	10,000

● Recommended Soldering Conditions



● Package Outline Dimensions (DFN1006-3L)



● Suggested Pad Layout

