




SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
PM2.0-UP1S-01A	1	0.00	2.00
PM2.0-UP1S-02A	2	2.00	4.00
PM2.0-UP1S-03A	3	4.00	6.00
PM2.0-UP1S-04A	4	6.00	8.00
PM2.0-UP1S-05A	5	8.00	10.00
PM2.0-UP1S-06A	6	10.00	12.00
PM2.0-UP1S-07A	7	12.00	14.00
PM2.0-UP1S-08A	8	14.00	16.00
PM2.0-UP1S-09A	9	16.00	18.00
.....			
PM2.0-UP1S-40A	40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	X.*± 5°	APR. Alex	TITLE: 2.0FH H4.3 2xnPin 180度 W4.5 U型 PC2.8 6T		
.XX±0.20	.X.*± 3°	CHK. Jack	DWG NO. PM2.0-UP1S-NA		
.XXX±0.10	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/3