





SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for 5 seconds)



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
B200N01-0B1P51-H43C28	1	0.00	2.00
B200N01-0B2P51-H43C28	2	2.00	4.00
B200N01-0B3P51-H43C28	3	4.00	6.00
B200N01-0B4P51-H43C28	4	6.00	8.00
B200N01-0B5P51-H43C28	5	8.00	10.00
B200N01-0B6P51-H43C28	6	10.00	12.00
B200N01-0B7P51-H43C28	7	12.00	14.00
B200N01-0B8P51-H43C28	8	14.00	16.00
B200N01-0B9P51-H43C28	9	16.00	18.00
.....			
B200N01-0B40P51-H43C28	40	(40-1)x2.0	(40)x2.0

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. B200N01-0BXP51-H43C28	TITLE: 2.0FH H4.3 1xnPin 180 度 W2.4 U型 PC2.8 6T		
.XX ±0.20	X.* ±1°				
.XXX ±0.10	X.XX* ±0.5°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1