

MSKSEMI 美森科

SEMICONDUCTOR



ESD



TVS



TSS



MOV



GDT



PLED

MS8002A

Product specification

概述

MS8002A 是一颗单通道 AB 类差分输入音频功率放大器。在 5.0V 电源供电，THD+N=10%，3 欧姆负载上可以输出 2.8W 的功率。

MS8002A 的差分输入架构能有效提高噪声的抑制能力。产品应用电路简单，仅需极少数的外围器件，就能提供高品质低失真的输出。

MS8002A 具有关断功能，极大的延长系统的待机时间。过热保护功能增强系统的可靠性。POP 声抑制功能改善了系统的听觉感受，同时简化系统调试。

MS8002A 提供 SOP8 封装



特性

- 输出功率：
 - 1.6W (VDD=5.0V, $R_L=8\Omega$, THD+N=10%)
 - 2.6W (VDD=5.0V, $R_L=4\Omega$, THD+N=10%)
 - 2.8W (VDD=5.0V, $R_L=3\Omega$, THD+N=10%)
- 工作电压：2.5V to 5.5V
- 低失真和低噪声
- 开机 POP 声抑制功能
- 过热保护功能


应用

- FM 播放器
- 网络摄像头
- 玩具及游戏机
- 插卡音箱/USB 音箱/蓝牙音箱


引脚描述和标记

SOP-8	引脚说明	管体标记
	 SD 1 Bypass 2 IN+ 3 IN- 4 8 OUTN 7 GND 6 VDD 5 OUTP	 MSKSEMI MS8002A MS**

单端输入典型应用电路图



差分输入典型应用电路图




管脚描述

管脚	符号	I/O	描述
1	SD	I	系统关断控制，默认高电平（高电平关机，低电平工作）
2	Bypass	I	参考电压
3	IN+	I	音频正输入端
4	IN-	I	音频负输入端
5	OUTP	O	音频正输出端口
6	VDD	P	电源
7	GND		地
8	OUTN	O	音频负输出端口

订货信息

料号	封装	包装
MS8002A	SOP8	4000颗/盘

功能框图



绝对最大额定值

V _{DD}	供电电压	-0.3V to 6V
V _I	输入电压	-0.3V to V _{DD} +0.3V
T _A	工作温度	-40°C to 85°C
T _J	结温	-40°C to 125°C
T _{STG}	储存温度	-65°C to 150°C
T _{SLD}	焊接温度	300°C, 5sec

注：绝对最大额定值是指设备的寿命受到损害的值，在绝对最大额定条件下会引起芯片的永久性损坏。

推荐额定值

			MIN	MAX	UNIT
V _{DD}	供电电压	VDD	2.5	5.5	V
V _{IH}	SD高电平	V _{DD} =5.0V	2		V
V _{IL}	SD低电平	V _{DD} =5.0V		0.6	V
R _L MIN	最小负载	V _{DD} =5.0V	3		Ω

热阻参数

Parameter	Symbol	Package	MAX	UNIT
热阻(Junction to Ambient)	θ _{JA}	SOP8	115	°C/W
热阻 (Junction to Case)	θ _{JC}		63	°C/W

电性参数


(VDD =5V, Gain=20dB, RL =8Ω, T =25°C, unless otherwise noted.)

Symbol	Parameter	Test Conditions		MIN	TYP	MAX	UNIT
Po	输出功率	THD+N=10%,f=1KHZ,RL=8Ω	VDD=5.0V		1.6		W
			VDD=4.2V		1.1		
			VDD=3.7V		0.85		
		THD+N=1%, f=1KHZ,RL=8Ω	VDD=5.0V		1.3		W
			VDD=4.2V		0.86		
			VDD=3.7V		0.66		
		THD+N=10%,f=1KHZ,RL=4Ω	VDD=5.0V		2.6		W
			VDD=4.2V		1.7		
			VDD=3.7V		1.3		
		THD+N=1%, f=1KHZ,RL=4Ω	VDD=5.0V		2.0		W
			VDD=4.2V		1.3		
			VDD=3.7V		1.0		
THD+N	总谐波失真 + 噪声	VDD=5.0V, Po=1.0W, RL=8Ω VDD=3.7V, Po=0.5W, RL=8Ω	f=1KHz		0.3		%
					0.4		
Gv	增益	Rin=27K , Rf=150K	VDD=3.7V		20		dB
PSRR	电源纹波抑制比	VDD=4.2V ±200mVp-p	f=1KHz		57		dB
SNR	信噪比	VDD=5.0V,Vorms=1V, Gv=20dB	f=1KHz		89		dB
Vn	残余噪声	VDD=5.0V,Input floating with Cin=0.1μF	A-weighting		35		μV
			No		53		
			A-weighting				
Dyn	动态范围	VDD=5.0V, THD=1%	f=1KHz		98		dB
Iq	静态电流	VDD=5.0V	VSD=0.3V No Load		5		mA
		VDD=4.2V			4		
		VDD=3.7V			3		
ISD	关断电流	VDD=2.0V to 5.0V	VSD=3.3V		1		μA
Vos	失调电压	VDD=5V, AC_GND			3		mV
Tst	启动时间	CBy = 1.0uF			90		mS
OTP	温度保护	Junction Temperature, No Load	VDD=5.0V		175		°C
OTH	迟滞温度				30		


典型特征曲线

(VDD = 5V, Gain=20dB, $R_L = 8\Omega$, T = 25°C, unless otherwise noted.)


THD+N vs Output Power




THD+N vs Output Power




THD+N VS Frequency




Frequency Response



PSRR



Noise Floor FFT



应用信息

输入电阻(Ri)

MS8002A 的增益由音量调节控制的输入电阻(RI)和反馈电阻(RF)控制。

增益计算如下：

$$A_v = 2 \times \frac{R_f}{R_i} \left(\frac{V}{V} \right)$$

其中，输入电阻RI为外部的输入电阻，Rf为外部反馈电阻。

输入电容 (Ci)

输入电容与输入电阻构成一个高通滤波器，其截至频率可由下式得出：

$$f_c = \frac{1}{(2\pi R_i C_i)}$$

Ci的值不仅会影响到电路的低频响应，而且也会影响电路启动和关断时所产生的POP声，输入电容越大，则到达其稳定工作点所需的电荷越多，在同等条件下，小的输入电容所产生的POP声比较小。

偏置电容CBYP

偏置电容是最关键的电容，它与几个重要性能相关，当电路启动时，偏置电容决定了放大器的开启速度，偏置电容同时会影响到电路的噪声和电源抑制比以及开关机的POP声。

为避免启动时的POP声，偏置电压的上升速度应该比输入偏置电压的上升速度慢。


关断工作模式

为了减少在关断模式下的功率损耗，MS8002A 带有关闭放大器偏置的关断电路。当SD引脚为低电平时，放大器正常工作。当SD引脚为高电平时，放大器被关闭，工作电流达到最小；SD引脚默认高电平。

过温保护

MS8002A带有过温保护电路以防止内部温度超过175℃时器件损坏。在不同器件之间，这个值有25℃的差异。当内部电路超过设置的保护温度时，器件进入关断状态，输出被截止。当温度下降 30℃后，器件重新正常工作。

封装图（SOP8）



符号	毫米（mm）		英寸（Inch）	
	最小值	最大值	最小值	最大值
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	1.550	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.27(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050

Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specification of any and all MSKSEMI Semiconductor products described or contained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringement of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.