



Features

- Ultra low capacitance: 0.4pF typical (I/O to I/O)
- Ultra low leakage: nA level
- Low operating voltage: 3.3V
- Low clamping voltage with snap back technology
- Up to 4 lines protects
- Leadless flow -through package
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
Air discharge: ± 30 kV
Contact discharge: ± 30 kV
 - IEC61000-4-4 (EFT) 40A (5/50ns)
 - IEC61000-4-5 (Lightning) 5A (8/20 μ s)
- RoHS Compliant

Dimensions DFN2510P10



Pin Configuration



Applications

- HDMI 1.3 & 1.4, USB 2.0 & 3.0 and MDDI ports
- Monitors and flat panel displays
- Set-top box and Digital TV
- Video graphics cards
- Digital Video Interface (DVI)
- Notebook Computers
- PCI Express and Serial SATA Ports

Mechanical Characteristics

- Package: DFN2510P10
- Lead Finish: Matte Tin
- UL Flammability Classification Rating 94V-0
- Quantity Per Reel: 3000pcs
- Reel Size: 7inch
- Device Marking: 3324


Absolute Maximum Ratings (T_{amb}=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μ s)	P _{pp}	60	W
ESD per IEC 61000-4-2 (Air)	V _{ESD}	± 30	kV
ESD per IEC 61000-4-2 (Contact)		± 30	
Operating Temperature Range	T _J	-55 to +125	°C
Storage Temperature Range	T _{STJ}	-55 to +150	°C


Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	VRWM			3.3	V	Any I/O pin to ground
Breakdown Voltage	VBR	4.5			V	It = 1mA, any I/O pin to ground
Reverse Leakage Current	IR			0.5	μA	VRWM = 3.3V, any I/O pin to ground
Clamping Voltage	VC			6.5	V	I _{PP} = 1A (8 x 20μs pulse), any I/O pin to ground
Clamping Voltage	VC			10	V	I _{PP} = 5A (8 x 20μs pulse), any I/O pin to ground
Junction Capacitance	CJ		0.4		pF	VR = 0V, f = 1MHz, between I/O pins
Junction Capacitance	CJ		0.6		pF	VR = 0V, f = 1MHz, any I/O pin to ground



Characteristic Curves




Junction Capacitance vs. Reverse Voltage



Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. Peak Pulse Current



8 X 20uS Pulse Waveform

Power Derating Curve




ESD Clamping Voltage


8 kV Contact per IEC61000-4-2

Typical Application


The LM-AZ1123-04F is designed for easy PCB layout by allowing the traces to run straight through the device. The PCB traces could be used to connect the pin pairs for each line. For example, line 1 enters at pin 1 and exits at pin 10 and the PCB trace connects Pin 1 and Pin 10 together. Ground is connected at Pin 3 and Pin 8.




LM-AZ1123-04F on USB 3.0 Port Application




LM-AZ1123-04F on DVI Port Application




LM-AZ1123-04F on HDMI Port Application




LM-AZ1123-04F on MDDI Port Application




LM-AZ1123-04F on 10/100 Base Ethernet Port Application




LM-AZ1123-04F on VGA Port Application



LM-AZ1123-04F on eSATA Port Application




DFN2510P10 Package Outline Drawing



DIM	INCHES			MILLIMETERS		
	MIN	NOM	MAX	MIN	NOM	MAX
A	.020	.023	.026	0.50	0.58	0.65
A1	0.00	.001	.002	0.00	0.03	0.05
A2		(.005)			(0.13)	
b	.006	.008	.010	0.15	0.20	0.25
b1	.014	.016	.018	0.35	0.40	0.45
D	.094	.098	.102	2.40	2.50	2.60
E	.035	.039	.043	0.90	1.00	1.10
e	.020 BSC			0.50 BSC		
L	.012	.015	.017	0.30	0.38	0.425
N	10			10		
aaa	.003			0.08		
bbb	.004			0.10		

Suggested Land Pattern



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
C	(.034)		(0.875)	
G	.008		0.20	
P	.020		0.50	
P1	.039		1.00	
X	.008		0.20	
X1	.016		0.40	
Y	.027		0.675	
Y1	(.061)		(1.55)	
Z	.061		1.55	

NOTICE

Leiditech reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Leiditech does not assume any liability arising out of the application or use of any product described herein.