

Features

- Ultra low leakage: nA level
- Operating voltage: 24V
- Low clamping voltage
- 2-pin leadless package
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
 - Air discharge: $\pm 30\text{kV}$
 - Contact discharge: $\pm 30\text{kV}$
 - IEC61000-4-4 (EFT) 80A (5/50ns)
 - IEC61000-4-5 (Lightning)35A (8/20 μs)
- RoHS Compliant


Applications

- Mobile Phones and Accessories
- Battery Protection
- USB VBus
- Power Line Protection
- Hand Held Portable Applications


Mechanical Characteristics

- Package: DFN1610-2
- Lead Finish: NiPdAu
- Case Material: "Green" Molding Compound.
- UL Flammability Classification Rating 94V-0
- Quantity Per Reel:3,000pcs
- Reel Size:7 inch
- Device Marking: 24P

Dimensions DFN1610-2



Pin Configuration




Absolute Maximum Ratings (T_{amb}=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs)	Ppk	1750	W
ESD per IEC 61000-4-2 (Air)	V _{ESD}	± 30	kV
ESD per IEC 61000-4-2 (Contact)		± 30	
Operating Temperature Range	T _J	-40 to +125	°C
Storage Temperature Range	T _{STJ}	-55 to +150	°C


Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				24	V
Breakdown Voltage	V_{BR}	$I_T = 1mA$	26		31	V
Reverse Leakage Current	I_R	$V_{RWM} = 24V$		<50	200	nA
Clamping Voltage	V_C	$I_{PP} = 1A$ (8 x 20 μs pulse)			33	V
Clamping Voltage	V_C	$I_{PP} = 35A$ (8 x 20 μs pulse)		35	44	V
Junction Capacitance	C_J	$V_R = 0V$, $f = 1MHz$		200	300	pF


Typical Performance Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise Specified)



8 / 20us Pulse Waveform




IEC61000-4-2 Pulse Waveform




Power Derating Curve

DFN1610- 2 Package Outline Drawing




TOP VIEW

SYM	DIMENSIONS					
	MILLIMETERS			INCHES		
	Min	Typ	Max	Min	Typ	Max
A	0.50	0.55	0.60	0.0197	0.0217	0.0236
A1	0.00	0.03	0.05	0.0000	0.0012	0.0020
b	0.75	0.80	0.85	0.0295	0.0315	0.0335
c	0.152 REF			0.0060 REF		
D	0.95	1.00	1.05	0.0374	0.0394	0.0413
e	1.09 REF			0.0429 REF		
E	1.55	1.60	1.65	0.0610	0.0630	0.0650
L	0.35	0.40	0.45	0.0138	0.0157	0.0177




BOTTOM VIEW



SIDE VIEW

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X1	1.700	0.0669
X2	0.600	0.0236
X3	0.500	0.0197
Y1	1.000	0.0394

NOTICE

Leiditech reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Leiditech does not assume any liability arising out of the application or use of any product described herein.