



- This reference specification applies to Chip Common Mode Choke Coil DLW21SN_SQ Series.
- Operating Temperature:-40~ +85℃
- Storage Temperature:-40~ +85℃

Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	Withstand Volt. (Vdc) max.	IR (Ω) min.
DLW21SN900SQ2L T	90 ± 25%	100	0.35	330	50	125	10M


MECHANICAL




TAPING AND PACKING




SCHEMATICS



IMPEDEDANCE FREQUENCY



Reel



Quantity (pcs):
3000 PCS PER REEL
5 REELS PER CARTON
15000PCS PER CARTON

Dimensions in mm

Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
Tel:0755-27652992 29016433 E-mail: sales1@cd-tek.com Website:www.cd-tek.com