



产品承认书

SPECIFICATION FOR APPROVAL

客户名称:

CUSTOMER

我司料号:

OUR PART NO.

XRR6H-6*10-2.0T

我司品名:

OUR PART NAME

Six-hole magnetic beads

送样日期:

DATE SAMPLES

数量:

QUANTITY

制造确认 MANUFACTURER APPROVE

拟制 DRAWN	审核 CHECKED	确认 APPROVED
Hufangting	Raoping	Lizhengxiong

客户确认 CUSTOMER APPROVE

客户名称 CUSTOMER NAME:

客户料号 CUSTOMER P/N:

规格型号 DESCRIPTION:

6*10-2.0T Six-hole dual circuit magnetic beads

检查结果: ☐ 合格 ☐ 不合格

签名及盖章:

INSPECT RESULT ACCEPT REJECT

SIGNATURE AND STAMP

说明 REMARK:

如对本承认书内容有异议请提出或标记发送至我司, 本承认书在未收到异议回复时于本承认书提供一周后生效。

If you have any objection to the contents of this acknowledgment, please raise it or send the mark to us. The acknowledgment will become effective one week after the acknowledgment is provided in the absence of any objection.

东莞市祥如电子有限公司

DONGGUAN XIANGRU ELECTRONICS CO., LTD

Tel: 0769-86346548 Fax: 0769-86346358



Email: dgxiangru@126.com

产品承认书
SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2024/10/08
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	6*10-2.0T Six-hole dual circuit magnetic beads
我司物料编号 OUR PART NO	XRR6H-6*10-2.0T	我司品名 OUR PART NAME	Six-hole magnetic beads

外观尺寸 Appearance of size

单位 Unit: mm



A	6.0±0.5	B	10.0±0.5	C	21.0±2.0	D	0.5±0.1	F	14.5Max		
---	---------	---	----------	---	----------	---	---------	---	---------	--	--

绕线N1 S-F: CP0.5 2.0TS

材料表MATERIAL LIST:

名称name	规格norm		MANUFACTURER		
磁珠 ferrite bead	F2-R6H6X10		PENGLING OR OTHER MANUFACTURER		
线材wire	CP0.5		YEHUA OR OTHER MANUFACTURER		
塑料袋 plastic bags	PE胶袋16X16/单面10C/环保PE		YISHENGDA OR OTHER MANUFACTURER		
PE袋（PCS）：		吸塑盘（PCS）：	内盒（PCS）：	外箱（PCS）	/
500PCS/1PE袋		/		10K/件	



产品承认书
SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2024/10/08
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	6*10-2.0T Six-hole dual circuit magnetic beads
我司物料编号 OUR PART NO	XRR6H-6*10-2.0T	我司品名 OUR PART NAME	Six-hole magnetic beads

电性能参数Electrical Performance Parameters:

项目sports event	规格norm	公差 tolerance	实测值 measured value	测试频率 Test Frequency	测试仪器 Testing Instruments
Z1	300 Ω	Min	350Ω	25MHZ	HP4191A
Z2	550 Ω	Min	610Ω	100MHZ	HP4191A

重要控制项Significant controls:

(1) 产品要求环保、无卤。The products are required to be environmentally friendly and halogen-free.	(3) 线圈两端弧形高度（F尺寸）各自控制在1.5mm以内。The height of the arc at each end of the coil (F dimension) is controlled within 1.5mm each.
(2) 产品穿线时不允许刮伤露铜，不允许短路，穿线方向不允许变动.Product threading is not allowed to scratch the exposed copper, not allowed to short-circuit, the direction of threading is not allowed to change.	(4) 外观保持清洁干净。 Exterior is kept clean and clear

存储条件 Storage conditions

- (1) 存放货物的库房应满足以下条件：温度：23℃, 相对湿度：63%。The warehouse where the goods are stored shall meet the following conditions: Temperature: 23℃, Relative humidity: 63%.
- (2) 禁止将产品保管在腐蚀性物质中，否则将引起端头氧化，导致降低焊接性。It is prohibited to store the product in corrosive substances, as this will cause oxidation of the ends, resulting in reduced weldability.
- (3) 为了避免受潮气、灰尘等物质的影响，产品应保管于货架上。In order to avoid the influence of moisture, dust and other substances, the products should be kept on the shelf.
- (4) 产品保管在库房中，应避免热冲击、振动以及直接光照等等。Products stored in the warehouse, should avoid thermal shock, vibration and direct light, etc.
- (5) 产品应密封包装。The product should be sealed and packaged

制表 MADE	审核 CHECKED	批准 APPROVED	
Hufangting	Raoping	Lizhengxiong	