








REV	L/TR	DESCRIPTION	DATE	APPROVED
A0		依新料号编码原则发行图面	20160406	

- NOTES:
1. HOUSING: LCP, UL 94V-0, COLOR- BLUE (PANTONE 300C) OR BLACK
 2. BOTTOM COVER: LCP, UL 94V-0,COLOR- BLUE (PANTONE 300C) OR BLACK
 3. CONTACT: USB3 C2680-H T=0.25mm ; USB2 C5191-H T=0.25mm
30μ" MIN. GOLDPLATED ON CONTACT AREA, 120μ" MIN. MATTE TIN
PLATED ON SOLDERING TAIL,80μ" MIN. NICKEL UNDER-PLATED OVERALL
 4. FRONT SHELL: SUS304-1/2H, T=0.25mm, 30μ" MIN. NICKEL PLATED OVER ALL,
100μ" MIN. MATTE TIN PLATED ON SOLDERING TAIL,
 5. MIDDLE SHELL: SUS304-1/2H, T=0.25mm,
 6. REAR SHELL: SUS304-1/2H, T=0.20mm,
 7. THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS
PER DIRECTIVE 2011/65/EU FOR ROHS COMPLIANT. OR PER IEC
61249-2-21 FOR HALOGEN-FREE COMPLIANT.




广东富盈兴业精密科技实业有限公司

品名 TITLE:		比例 SCALE	图号 DWG NO.:	
■ RoHS	■ HF	TYPE-C 双层 24P母座 90度四脚全插	1:1	
TOLERANCE (UNLESS SPECIFIED)		FY23-70TC482F1175-01	张数 SHEET	1/1
.0 ±0.30	0.° ±10°	审核 APPROVE BY:	版本 VER.	单位 UNITS: mm
.00 ±0.20	0.° ±8°	设计 DESIGN BY:	2.0	
XU100 ±0.10	0.0° ±5°	1 i	XU1 i	

REV	LTR	DESCRIPTION	DATE	APPROVED
A0		依新料号编码原则发行图面	20160406	

USB TYPE-C FULL-FEATURED RECEPTACLE INTERFACE PIN ASSIGNMENTS

PIN	Signal Name	Description	PIN	Signal Name	Description
A1	GND	Ground return	B12	GND	Ground return
A2	SSTXp1	Positive half of first SuperSpeed TX differential pair	B11	SSRXp1	Positive half of first SuperSpeed RX differential pair
A3	SSTXn1	Negative half of first SuperSpeed TX differential pair	B10	SSRXn1	Negative half of first SuperSpeed RX differential pair
A4	Vbus	Bus Power	B9	Vbus	Bus Power
A5	CC1	Configuration Channel	B8	SB12	Sideband Use (SBU)
A6	Dp1	Positive half of the USB 2.0 differential pair-Position 1	B7	Dn2	Negative half of the USB 2.0 differential pair-Position 2
A7	Dn1	Negative half of the USB 2.0 differential pair-Position 1	B6	Dp2	Positive half of the USB 2.0 differential pair-Position 2
A8	SB11	Sideband Use (SBU)	B5	CC2	Configuration Channel
A9	Vbus	Bus Power	B4	Vbus	Bus Power
A10	SSRXn2	Negative half of second SuperSpeed RX differential pair	B3	SSTXn2	Negative half of second SuperSpeed TX differential pair
A11	SSRXp2	Positive half of second SuperSpeed RX differential pair	B2	SSTXp2	Positive half of second SuperSpeed TX differential pair
A12	GND	Ground return	B1	GND	Ground return






RECOMMENDED PCB LAYOUT(TOP VIEW)
(DEFAULT TOLERANCE:±0.05)

广东富盈兴业精密科技实业有限公司

品名 TITLE:		比例 SCALE		图号 DWG NO.:	
TYPE-C 双层 24P母座 90度四脚全插		1:1			
FY23-70TC482F1175-01		张数		1/1	
TOLERANCE (UNLESS SPECIFIED)		SHEET			
0.±0.30		审核 APPROVE BY:		版本	
.00±0.20		设计DESIGN BY:		2.0	
0.°±10°		li		单位	
.0°±8°		xuli		UNITS: mm	
.00°±5°					
xuli00±0.10					
TOLERANCE					
Rohs		HF			

REV	LTR	DESCRIPTION	DATE	APPROVED
A0		依新料号编码原则发行图面	20160406	






產品

1、將產品整齊擺放脆盤中,共50PCS.

2、裝滿一盤產品後,將蓋子蓋上。

3、將裝滿產品的脆盤疊放14層；然後用打包膜捆綁(共700PCS)。



6、用膠紙工字型封住紙箱，一共1400PCS產品。

5、將產品2捆並排放入紙箱，上下各放一紙板。

4、將每14層捆綁好的產品裝入一個防水袋，加入一袋干燥劑。

作業步驟：

- 1、將產品整齊放入脆盤中，共50PCS，再蓋上蓋子。
- 2、將裝滿50PCS產品的脆盤疊放14盤，用打包膜捆綁。
- 3、將捆綁好的产品放入防水袋中，再放入1袋乾燥劑，膠帶封口(共700PCS)。
- 4、在紙箱底先放一個紙板，然後將捆好的产品並排放入紙箱，頂層再放一個紙板。
- 5、合上紙箱後，再用膠帶工字型將紙箱封口，整箱共1400PCS產品。
- 6、貼上出貨標籤，如有零數箱需做標識。
- 7、紙箱材質尺寸：PS防靜電 275*160*14.5mm

脆盤材質尺寸：PS防靜電 275*160*14.5mm

广东富盈兴业精密科技实业有限公司

品名 TITLE:		比例 SCALE		图号 DWG NO.:	
TYPE-C 双层 24P母座 90度四脚全插		1:1			
FY23-70TC482F1175-01		张数 SHEET		1/1	
审核 APPROVE BY:		设计 DESIGN BY:			
li		xuli			
版本 VER.		2.0		单位 UNITS: mm	

■ Rohs	■ HF
TOLERANCE (UNLESS SPECIFIED)	
0.±0.30	0.°±10°
.00±0.20	.0°±8°
xu100±0.10	.00°±5°