

General Description

The CMH4332P uses advanced planar stripe DMOS technology and design

to provide excellent RDS(ON) .

These devices are well suited for high efficient switched mode power supplies and active power factor correction.

Features

- Low on-resistance
- Fast Switching
- RoHS Compliant



Product Summary

BVDSS	R _{DS(on)} max.	ID
250V	38mΩ	90A

Applications

- DC-AC converters
- SMPS Power
- UPS (Uninterruptible Power Supply)

TO-247 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	250	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current	90	A
I _D @T _C =100°C	Continuous Drain Current	66	A
I _{DM}	Pulsed Drain Current	360	A
EAS	Single Pulse Avalanche Energy ¹	3515	mJ
P _D @T _C =25°C	Total Power Dissipation	550	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient	---	40	°C/W
R _{θJC}	Thermal Resistance Junction-case	---	0.49	°C/W

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	250	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=40A$	---	29	38	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	---	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=250V$, $V_{GS}=0V$	---	---	25	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	±100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	48	---	S
Q_g	Total Gate Charge	$I_D=82A$	---	125	---	nC
Q_{gs}	Gate-Source Charge	$V_{DS}=250V$	---	45	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$	---	50	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=125V$	---	80	---	ns
T_r	Rise Time	$I_D=82A$	---	26	---	
$T_{d(off)}$	Turn-Off Delay Time	$R_G=25\Omega$	---	295	---	
T_f	Fall Time	$V_{GS}=15V$	---	80	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	7000	---	pF
C_{oss}	Output Capacitance		---	780	---	
C_{rss}	Reverse Transfer Capacitance		---	70	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	90	A
I_{SM}	Pulsed Source Current		---	---	360	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=40A$, $T_J=25^{\circ}\text{C}$	---	0.86	1.5	V
t_{rr}	Reverse Recovery Time	$di/dt = 100A/\mu s$	---	324	---	ns
Q_{rr}	Reverse Recovery Charge	$V_{GS}=0V$, $I_{SD}=82A$	---	21	---	μC

Note :







1.The EAS data shows Max. rating . The test condition is $V_{DD}=80V$, $V_{GS}=10V$, $L=5mH$, $I_{AS}=37.5A$.

This product has been designed and qualified for the consumer market.






Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.

Typical Characteristics




Typical Characteristics



Package Dimension

TO-247

Unit :mm



符号	机械尺寸/mm			符号	机械尺寸/mm		
	最小值	典型值	最大值		最小值	典型值	最大值
A	4.80	5.00	5.20	E2		5.00	
A1	2.21	2.41	2.61	E3		2.50	
A2	1.90	2.00	2.10	e		5.44	
b	1.10	1.20	1.35	L	19.42	19.92	20.42
b1		2.00		L1		4.13	
b2		3.00		P	3.50	3.60	3.70
c	0.55	0.60	0.75	P1		7.19	
D	20.80	21.00	21.20	P2		2.50	
D1		16.55		Q		5.80	
D2		1.20		S	6.05	6.15	6.25
E	15.60	15.80	16.0	T		10.00	
E1		13.30		U		6.20	