





- 1.High common mode impedance at high frequency Effects excellent noise suppression performance
- 2.100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 3.Operating temperature-40~+85 C (Including self - temperature rise)


Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	Withstand Volt. (Vdc) max.	IR (Ω) min.
LC2012A801T J	800±25%	100	0.88	300	50	125	10M

MECHANICAL



Dimension : mm

TAPING AND PACKING




Quantity (pcs):

10000 PCS PER REEL


5 REELS PER CARTON

50000PCS PER CARTON


SCHEMATICS



IMPEDEANCE
FREQUENCY



Reel



Dimensions in mm