






ROHS G103



Pin1



RECOMMENDED PCB LAYOUT
(TOLERANCE:±0.10)

1.ELECTRICAL SPECIFICATIONS:

- 1.1 Rated current and voltage(额定电流):
2.0A 100V AC(r.m.s)
- 1.2 Dielectric Withstanding Voltage(耐电压) :
800V AC for one minute
- 1.3 Contact Resistance(接触电阻) :
20mΩ max
- 1.4 Insulation Resistance(绝缘电阻) :
1000MΩ min
- 1.5 Operating Temperature(工作温度) :
-25℃ ~ 85℃

2.MATERIAL SPECIFICATION:

- 2.1 Insulator Material(绝缘体材质):
PA66 (nature)
- 2.2 Contact Material(端子材质):
Brass
- 2.3 Applicable wire:30AWG TO 24AWG

▲ Non-tooled parts No.of positions DIM list:

CONTACTS	DIMENSIONS	
	A	B
2	2.00	6.10
3	4.00	8.10
4	6.00	10.10
5	8.00	12.10
6	10.00	14.10
7	12.00	16.10
8	14.00	18.10
9	16.00	20.10
10	18.00	22.10
11	20.00	24.10
12	22.00	26.10
13	24.00	28.10
14	26.00	30.10
15	28.00	32.10
16	30.00	34.10

PART NO. LEGEND:
WB2032DS-XXT2

Insulator Material: 2:PA66
Contact Plating :T:Tin all Over
NO of Contacts: 2 to 16
Welding Method:DS=DIP180°
Wafer Conn

DRAWING:
Hu yatao

CHECKED:
Tony

APPROVAL:
Yang jie

GENERAL TOLERANCE


.X:=±0.30 .X*:=±2°
.XX:=±0.20 .XX*:=±1°
.XXX:=±0.10 .XXX*:=±0.5°

UNIT: MM

SCALE: N/A

SHEET: 1/1

PROJECTION:



CHIN-BAN
electronics (H.K.) co., ltd

DESCRIPTION:

2.00mm Pitch DIP180° K Series

PART NO: WB2032DS-XXT2

REV: 1.0

CUSTOMER NO:

SIZE: A4