

SOD-123 Schottky Barrier Rectifier Diode 肖特基势垒整流二极管

■Features 特点

Low forward voltage drop 低正向压降
High current capability 高电流能力
Surface mount device 表面贴装器件
Case 封装:SOD-123



■Maximum Rating 最大额定值

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	B5817W -6AF	B5818W -6AF	B5819W -6AF	Unit 单位
Device Marking 产品印字		SJ	SK	SL	
Peak Reverse Voltage 反向峰值电压	V_{RRM}	20	30	40	V
DC Reverse Voltage 直流反向电压	V_R	20	30	40	V
RMS Reverse Voltage 反向电压均方根值	$V_{R(RMS)}$	14	21	28	V
Forward Rectified Current 正向整流电流	I_F	1			A
Peak Surge Current 峰值浪涌电流	I_{FSM}	25			A
Repetitive Peak Surge Current 重复峰值浪涌电流	I_{FRM}	3			A
Power Dissipation 耗散功率	P_D	250			mW
Thermal Resistance J-A 结到环境热阻	$R_{\theta JA}$	400			$^{\circ}\text{C}/\text{W}$
Junction Temperature 结温	T_J	$-65\text{to}+125$			$^{\circ}\text{C}$
Storage Temperature 储藏温度	T_{stg}	$-65\text{to}+150$			$^{\circ}\text{C}$

■Electrical Characteristics 电特性

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	B5817W -6AF	B5818W -6AF	B5819W -6AF	Unit 单位	Condition 条件
Reverse Voltage 反向电压	V_R	20	30	40	V	$I_R=1\text{mA}$
Forward Voltage 正向电压	V_F	0.45 0.75	0.5 0.875	0.55 0.9	V	$I_F=1\text{A}$ $I_F=3\text{A}$
Reverse Current 反向电流	I_R	0.05 ($T_A=25^{\circ}\text{C}$) 8 ($T_A=100^{\circ}\text{C}$)			mA	$V_R=V_{RRM}$
Diode Capacitance 二极管电容	C_T	30			pF	$V_R=4\text{V}, f=1\text{MHz}$

■ Typical Characteristic Curve 典型特性曲线

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.3 - Power Derating Curve




FIG.4-TYPICAL JUNCTION CAPACITANCE




FIG.2-TYPICAL FORWARD

CHARACTERISTICS






FIG.5 - TYPICAL REVERSE

CHARACTERISTICS



■ **Dimension 外形封装尺寸**



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	2.600	2.800	0.102	0.110
B	1.500	1.700	0.059	0.067
C	1.050	1.150	0.041	0.045
C1	0.600	0.700	0.024	0.028
D	3.550	3.850	0.140	0.152
L	0.250	0.450	0.010	0.018
b	0.450	0.650	0.018	0.026
h	0.020	0.120	0.001	0.005
θ 3	0°	7°	0°	7°