



PART NO. AND CH. CODE	$\Delta W_{\pm 0.4}$	$\Delta W_{\pm 0.4}$	H ₁	H ₂	A ₁	A ₂	B	Δ WIRE SIZE
7114-4030	2. 90	3. 90	Δ (2. 62)	Δ (3. 43)	3. 00	1. 70	6. 20	AVS/AVSS/CAVS 0. 3~0. 5 CHFUS 0. 35~0. 5, HFSS 0. 5
7114-4031	3. 60	4. 70	Δ (3. 34)	Δ (4. 20)	4. 00	1. 70	7. 20	AVS 0. 5~1. 25, AVSS 0. 75~1. 25 CAVS 0. 85~1. 25, CHFUS/HFSS 0. 75~1. 5
7114-4032	4. 90	6. 40	Δ (4. 62)	Δ (5. 66)	4. 00	1. 70	7. 20	AVS 2~3 HFSS 2, HF 3



SEC. K-K

SEC. M-M



SEC. C-C

Δ 10. 03. 29	CHANGED NAME, ETC.	C10-Z186	T. 0	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	Δ BRASS (t=0. 40)	TREAT.	Δ TIN PLATING	ISSUE MARK
Δ 98. 07. 18	CHANGED FORM & DIMENSION	C97-N459	H. K	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	Δ BRASS (t=0. 40)	TREAT.	Δ TIN PLATING	ISSUE MARK
88. 12. 24	NEW	C89-L001	K. J	OFFICE	TRIAL PART NO.		NAME	Δ 4. 8 (187)	TERMINAL	MALE	
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR		NAME	Δ 4. 8 (187)	TERMINAL	MALE	
GENERAL TOLERANCE											
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG. TYPE	DWG. SOURCE	DWG. DATE	UNIT	SCL
A $\pm 0. 15$	$\pm 0. 2$	$\pm 0. 3$	$\pm 0. 5$	$\pm 0. 75$	$\pm 30^\circ$	0. 1	R	NEW	88. 11. 14	mm	5: 1
B $\pm 0. 2$	$\pm 0. 3$	$\pm 0. 55$	$\pm 0. 95$	$\pm 1. 4$	$\pm 30^\circ$	0. 1	APPROVED	CHECKED	DESIGN	DRAWN	3
C $\pm 0. 3$	$\pm 0. 5$	$\pm 0. 8$	$\pm 1. 4$	± 2	$\pm 30^\circ$	0. 15	M. FUKUDA	T. MIWA	T. OSADA	SUEYOSHI	M. MORAL
SPECIFIED							MASS				
10. 03. 29							10. 03. 29	10. 03. 29	10. 03. 29	87. 03. 04	10. 03. 29
YAZAKI CORPORATION											

注 記
1. 対応品番: 7116-4030 ETC.

NOTE
1. MATING PART NO.: 7116-4030 ETC.

