

SOD-123 Schottky Barrier Rectifier Diode 肖特基势垒整流二极管

■Features 特点

High current capability 高电流能力

Low forward voltage drop 低正向压降

Guard Ring Construction for Transient Protection 瞬态保护环结构

Case 封装:SOD-123



■Maximum Rating 最大额定值

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)




Characteristic 特性参数	Symbol 符号	B0520LW -6AF	B0530W -6AF	B0540W -6AF	Unit 单位
Device Marking 产品印字		SD	SE	SF	
Peak Reverse Voltage 反向峰值电压	V_{RRM}	20	30	40	V
Peak Reverse Working Voltage 反向峰值工作电压	V_{RWM}	20	30	40	V
DC Reverse Voltage 直流反向电压	V_R	20	30	40	V
RMS Reverse Voltage 反向电压均方根值	$V_{R(RMS)}$	14	21	28	V
Forward Rectified Current 正向整流电流	I_F	0.5			A
Peak Surge Current 峰值浪涌电流	I_{FSM}	5.5			A
Power Dissipation 耗散功率	P_D	500			mW
Thermal Resistance J-A 结到环境热阻	$R_{\theta JA}$	250			$^{\circ}\text{C}/\text{W}$
Junction/Storage Temperature 结温/储藏温度	T_J, T_{stg}	$-50\text{to}+150$			$^{\circ}\text{C}$

■Electrical Characteristics 电特性

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	B0520LW -6AF	B0530W -6AF	B0540W -6AF	Unit 单位	Condition 条件
Reverse Voltage 反向电压	V_R	20	30	40	V	$I_R=250\mu\text{A}$ $I_R=200\mu\text{A}$ $I_R=20\mu\text{A}$
Forward Voltage 正向电压	V_F	0.32 0.385	0.375 0.43	0.51 0.62	V	$I_F=0.1\text{A}$ $I_F=0.5\text{A}$ $I_F=1\text{A}$
Reverse Current 反向电流	I_R	75 250	20 130	10 20	μA	$V_R=10\text{V}$ $V_R=15\text{V}$ $V_R=20\text{V}$ $V_R=30\text{V}$ $V_R=40\text{V}$
Diode Capacitance 二极管电容	C_T	170			pF	$V_R=4\text{V}, f=1\text{MHz}$

■ Typical Characteristic Curve 典型特性曲线



■ Dimension 外形封装尺寸 SOD-123

Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A	2.600	2.800	0.102	0.110
B	1.500	1.700	0.059	0.067
C	1.050	1.150	0.041	0.045
C1	0.600	0.700	0.024	0.028
D	3.550	3.850	0.140	0.152
L	0.250	0.450	0.010	0.018
b	0.450	0.650	0.018	0.026
h	0.020	0.120	0.001	0.005
Θ 3	0°	7°	0°	7°

