









RoHS



RECOMMENDED P.C.B LAYOUT



NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	High temperature material	UL94V-0 Black	1
2	CONTACT	Phosphor bronze	SURFACE PLATING: Au/TIN	1
3	SHELL	Stainless steel	SURFACE PLATING: TIN	1

NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS.

2. PRODUCT PERFORMANCE:

2.1 RATED VOLTAGE(MAX.):30V AC/DC

2.2 RATED CURRENT(MAX.):(2、3、4PIN)1.0A (1、5PIN)1.8A AC/DC

2.3 DIELECTRIC STRENGTH:100V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN

2.4 INSULATION RESISTANCE:1000 MΩ MIN. 100VDC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL

2.5 CONTACT RESISTANCE:30 mΩ MAX.

2.6 OPERATING TEMPERATURE:-30°C to +85°C

3.PART NO. LEGEND: 1U206-145005-0000X

WATER CODE:SEE NOTES

WATER CODE	NOTES
00001	SURFACE PLATING Au GF,SOLDER TAP PLATING Au GF
00002	SURFACE PLATING Au 30u",SOLDER TAP PLATING Au GF
00003	SURFACE PLATING Au 1u",SOLDER TAP PLATING Tin

7.0	2022.06.06	MODIFY PRODUCT NUMBER	ShunMingWen
6.0	2015.7.23	调整尺寸管控	Tian Hai
5.0	2015.4.15	增加电镀规格	Bains
4.0	2014.8.8	追加尺寸管控	Xiao Yong
3.0	2014.2.12	胶芯底部加胶	Simon
2.0	2013.10.8	修改图面描述	Simon
NO.	DATE	DESCRIPTION	DRAWING

DRAWING:	Bains
CHECKED:	Tian Hai
APPROVAL:	Cykin

GENERAL TOLERANCE

.X:=±0.30 .X':=±2°

.XX:=±0.20 .XX':=±1°


.XXX:=±0.10 .XXX':=±0.5°

UNIT: MM

PROJECTION:

SCALE: N/A

SHEET: 1/1

**CHIN-BAN**
Electronic Technology

DESCRIPTION: Micro USB 2.0 Conn. Female B Type 立式

PART NO: 1U206-145005-0000X

REV: 7.0

OLD CODE: U6F05D-CXT2-B4

DRAWING NO: UK0016

SIZE: A4