





COIL: @ 25°C
 RESISTANCE 1560 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.2 VDC
 MUST RELEASE 0.89 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX
 RELEASE TIME 4.0 MS MAX
 CONTACT BOUNCE TIME 15 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 1 AMP 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 10/20/99 (K. JERRY) 10/20/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. C. I. I. STD.

CUST. NO. REV.

SMGAD RELAY

SMGAD-26