









P.C.B LAYOUT



CIRCUIT: SPST ▲

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERM. NUMBERS FOR REF. ONLY.
4. RATING: 50mA @ 12VDC
- ▲ 5. OPERATING FORCE:  $160 \pm 50$ gf
6. TRAVEL:  $0.25 +0.2/-0.1$ mm
7. CONTACT RESISTANCE: 100 m $\Omega$  MAX.
- ▲ 8. CONTACT MATERIAL: SILVER
9. DIELECTRIC STRENGTH: 250V RMS min.
10. INSULATION RESISTANCE: 100 MEGA $\Omega$  min.
11. ELECTRICAL LIFE: 100,000 CYCLES
12. ▲ DENOTES CRITICAL PARAMETER.
13. OPERATING TEMP: -40°C to 85°C
14. PACKAGE: POLYBAG / 750 PIECES PER BAG



| REV | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®           |                |       |             | OBJECT ID |
|-----|------------|--------------|----------|----|---------------------|----------------|-------|-------------|-----------|
| C   | ECO-102176 | PRINT UPDATE | 08/31/23 | JS | TITLE TLE1105BF160Q |                |       |             | 000017684 |
|     |            |              |          |    | SCALE 4:1           | DATE 2/22/1995 | DR JL | DWG P010102 | REV C     |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED