


APPLICABLE OUTER CONDUCTOR CRIMPING TOOL : HT303/UM.MSS-T-1(1.5 HOLE)  
APPLICABLE CAP PRESS FITTING TOOL : P06-T-2



RoHS COMPLIANT

|     |                 |                  |     |                  |                          |
|-----|-----------------|------------------|-----|------------------|--------------------------|
| 5   | PHOSPHOR BRONZE | GOLD PLATING     |     |                  |                          |
| 4   | PTFE            |                  | 9   | POLYOLEFIN       | BLACKHEAT SHRINK TUBING) |
| 3   | BRASS           | GOLD PLATING     | 8   | COPPER           | NICKEL PLATING           |
| 2   | BRASS           | GOLD PLATING     | 7   | BRASS            | NICKEL PLATING           |
| 1   | BRASS           | GOLD PLATING     | 6   | BERYLLIUM COPPER | NICKEL PLATING           |
| NO. | MATERIAL        | FINISH . REMARKS | NO. | MATERIAL         | FINISH . REMARKS         |

|                                   |  |                |           |                              |          |         |      |
|-----------------------------------|--|----------------|-----------|------------------------------|----------|---------|------|
| UNITS<br>mm                       |  | SCALE<br>5 : 1 | COUNT<br> | DESCRIPTION OF REVISIONS     | DESIGNED | CHECKED | DATE |
| APPROVED : MH. YAMANE 12. 09. 21  |  |                |           | DRAWING NO. EDC4-136681-40   |          |         |      |
| CHECKED : TS. NOBE 12. 09. 21     |  |                |           | PART NO. P06(75)-LP-1.5C(40) |          |         |      |
| DESIGNED : TM. YOSHIDA 12. 09. 21 |  |                |           | CODE NO. CL328-0046-1-40     |          |         |      |
| DRAWN : SY. OUCHI 12. 09. 21      |  |                |           |                              |          |         |      |