

规格承认书

SPECIFICATION

编号(No):

日期(Date):

客户 (Customer):

品名(Product Name): 片式NTC热敏电阻 Chip NTC thermistor

恭成料号 (QAM Part Number): QN1206X104J4250FB

客户规格(Customer's Part Number):

客户承认 CUSTOMER CONFIRM			
承认章 STAMP	核准 APPROVE	审核 CHECK	经办人 SIGNATURE
			

恭成科技有限公司**Quest for Advanced Materials Electronics Co., Ltd.**

营销中心: 广东省深圳市龙华新区观澜银星科技大厦 518109

Domestic Marketing Center: Yinxing Technology Building, Guanlan, Longhua new district, Shenzhen 518109

电话 Tel: 0086-755-23732935 传真 Fax: 0086-755-23762516

制造中心: 河北省唐山市曹妃甸工业区中日生态园 063200

Manufactory: Sino-Japan Eco-industrial park, Caofeidian industrial district, Tangshan, Hebei, China 063200

电话 Tel: 0086-315-7332530

网址 Website: <https://www.qamcn.com>邮箱 E-Mail: qam@qamcn.com

变更履历表 **Version change history**

[illegible]

1 外形尺寸 Shape and Dimensions

- 尺寸：见图 1 和表 1
- PCB 焊盘：见图 2 和表 1
- Dimensions: See Fig.1 and Table 1.
- Recommended PCB pattern for reflow soldering: See Fig.2 and Table 1




图 1 Fig.1




图 2 Fig.2

表 1 (Table 1)

单位 unit: inch[mm]

类别 Type	L	W	T	a	A	B	C
1206 [3216]	0.126±0.008 [3.20±0.2]	0.063±0.008 [1.60±0.2]	0.033±0.008 [0.85±0.2]	0.020±0.012 [0.50±0.3]	1.8~2.5	1.0~1.5	1.2~2.0

2 产品标识 (料号) Product Identification(Part Number)

QN 1206 X 104 J 4250 F B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① 类别 Type	
QN	片式 NTC 热敏电阻器 Chip NTC Thermistor

② 外形尺寸(mm) External Dimensions (L×W×T)	
0201[0603]	0.60×0.30×0.30
0402[1005]	1.00×0.50×0.50
0603[1608]	1.60×0.80×0.80
0805[2012]	2.00×1.25×0.85
1206[3216]	3.20×1.60×0.85

③ 分隔符 Delimiter	
	X

④ 25℃的零功率电阻 Nominal Zero-Power Resistance	
222	2.2kΩ
473	47kΩ
104	100kΩ

⑤ 电阻值公差 Tolerance of Resistance	
F	±1%
G	±2%
H	±3%
J	±5%
K	±10%

⑥ B 值常数 B Constant	
3435	3435K
3950	3950K
4250	4250K

⑦ B 值公差 Tolerance of B Constant	
F	±1%
H	±3%

⑧ B 值计算方式 B constant calculation method	
A	25℃&85℃
B	25℃&50℃

3 电气特性 Electrical Characteristics

型号 Part No	电阻值 Resistance (25℃) (kΩ)	B 常数 B Constant (25/50℃) (K)	B 常数 B Constant (25/85℃) (K)	允许工作电流 Permissible Operating Current (25℃) (mA)	耗散系数 Dissipation Factor (mW/℃)	热时间常数 Thermal Time Constant (s)	额定功率 Rated Electric Power(25℃) (mW)	工作温度 Operating ambient temperature (℃)
QN1206X104J4250FB	100±5%	4250±1%	4311 ref.	0.21	3.0	<8	150	-40~+125

4 检验和测试程序

▪ 测试条件

如无特别规定，检验和测试的标准大气环境条件如下：

- 环境温度：20±15℃；
- 相对湿度：65±20%；
- 气压：86 kPa~106 kPa

如果对测试结果有异议，则在下述条件下测试：

- 环境温度：25±2℃；
- 相对湿度：65±5%；
- 气压：86kPa ~ 106kPa

▪ 检查设备

外观检查：20 倍放大镜；

阻值检查：热敏电阻测试仪

4 Test and Measurement Procedures

▪ Test Conditions

Unless otherwise specified, the standard atmospheric conditions for measurement/test as:

- Ambient Temperature: 20±15℃
- Relative Humidity : 65±20%
- Air Pressure: 86kPa to 106kPa

If any doubt on the results, measurements/tests should be made within the following limits:


- Ambient Temperature: 25±2℃
- Relative Humidity: 65±5%
- Air Pressure: 86kPa to 106kPa

▪ Inspection Equipment

Visual Examination: 20× magnifier




Resistance value test: Thermistor resistance tester


5 电性测试 Electrical Test

序号 No.	项目 Items	测试方法及备注 Test Methods and Remarks
1	25℃零功率电阻值 Nominal Zero-Power Resistance at 25℃(R25)	环境温度 Ambient temperature: 25±0.05℃ 测试功率 Measuring electric power: ≤0.1mW
2	B 值常数 Nominal B Constant	分别在环境温度 25±0.05℃, 50±0.05℃或 85±0.05℃下测量电阻值。 Measure the resistance at the ambient temperature of 25±0.05℃, 50±0.05℃ or 85±0.05℃. $B(25-50^{\circ}\text{C}) = \frac{\ln R_{25} - \ln R_{50}}{1/T_{25} - 1/T_{50}} \quad B(25-85^{\circ}\text{C}) = \frac{\ln R_{25} - \ln R_{85}}{1/T_{25} - 1/T_{85}}$ T: 绝对温度 (K) Absolute temperature (K)
3	热时间常数 Thermal Time Constant	在零功率条件下，当热敏电阻的环境温度发生急剧变化时，热敏电阻元件产生最初温度 T₀ 与最终温度 T₁ 两者温度差的 63.2% 的温度变化所需要的时间，通常以秒(S)表示。 The total time for the temperature of the thermistor to change by 63.2% of the difference from ambient temperature T₀ (°C) to T₁ (°C) by the drastic change of the power applied to thermistor from Non-zero Power to Zero-Power state, normally expressed in second(S). 

4	耗散系数 Dissipation Factor	在一定环境温度下，NTC 热敏电阻通过自身发热使其温度升高 1℃时所需要的功率，通常以 mW/℃表示。可由下面公式计算： The required power which makes the NTC thermistor body temperature raise 1℃ through self-heated, normally expressed in milliwatts per degree Celsius (mW/℃). It can be calculated by the following formula: $\delta = \frac{W}{T-T_0}$
5	额定功率 Rated Power	在环境温度 25℃下因自身发热使表面温度升高 100℃所需要的功率。 The necessary electric power makes thermistor's temperature rise 100℃ by self-heating at ambient temperature 25℃.
6	允许工作电流 Permissible operating current	在静止空气中通过自身发热使其升温为 1℃的电流。 The current that keep body temperature of chip NTC on the PC board in still air rising 1℃ by self-heating.

6 信赖性试验 Reliability Test

项目 Items	测试标准 Standard	测试方法及备注 Test Methods and Remarks	要求 Requirements																																				
端头附着力 Terminal Strength	IEC 60068-2-21	将晶片焊接在测试基板上（如右图所示的环氧玻璃布板），按箭头所示方向施加作用力； Solder the chip to the testing jig (glass epoxy board shown in the right) using eutectic solder. Then apply a force in the direction of the arrow. <table><tr><th>尺寸 Size</th><th>F</th><th>保持时间 Duration</th></tr><tr><td>0201</td><td>2N</td><td rowspan="3">10±1s</td></tr><tr><td>0402, 0603</td><td>5N</td></tr><tr><td>0805,1206</td><td>10N</td></tr></table>	尺寸 Size	F	保持时间 Duration	0201	2N	10±1s	0402, 0603	5N	0805,1206	10N	端电极无脱落且瓷体无损伤。 No removal or split of the termination or other defects shall occur. 																										
尺寸 Size	F	保持时间 Duration																																					
0201	2N	10±1s																																					
0402, 0603	5N																																						
0805,1206	10N																																						
抗弯强度 Resistance to Flexure	IEC 60068-2-21	将晶片焊接在测试基板上（如右图所示的环氧玻璃布板），按下图箭头所示方向施加作用力； Solder the chip to the test jig (glass epoxy board shown in the right) using a eutectic solder. Then apply a force in the direction shown as follow;  <table><tr><th>尺寸 Size</th><th>弯曲变形量 Flexure</th><th>施压速度 Pressurizing Speed</th><th>保持时间 Duration</th></tr><tr><td>0201,</td><td>1mm</td><td rowspan="3"><0.5mm/s</td><td rowspan="3">10±1s</td></tr><tr><td>0402, 0603,</td><td colspan="2" rowspan="2">2mm</td></tr><tr><td>0805,1206</td></tr></table>	尺寸 Size	弯曲变形量 Flexure	施压速度 Pressurizing Speed	保持时间 Duration	0201,	1mm	<0.5mm/s	10±1s	0402, 0603,	2mm		0805,1206	① 无外观损伤。 No visible damage. ② $\Delta R_{25}/R_{25} \leq 2\%$ 单位 unit: mm <table><tr><th>类型 Type</th><th>a</th><th>b</th><th>c</th></tr><tr><td>0201</td><td>0.25</td><td>0.3</td><td>0.3</td></tr><tr><td>0402</td><td>0.4</td><td>1.5</td><td>0.5</td></tr><tr><td>0603</td><td>1.0</td><td>3.0</td><td>1.2</td></tr><tr><td>0805</td><td>1.2</td><td>4.0</td><td>1.65</td></tr><tr><td>1206</td><td>2.0</td><td>5.8</td><td>1.9</td></tr></table> 	类型 Type	a	b	c	0201	0.25	0.3	0.3	0402	0.4	1.5	0.5	0603	1.0	3.0	1.2	0805	1.2	4.0	1.65	1206	2.0	5.8	1.9
尺寸 Size	弯曲变形量 Flexure	施压速度 Pressurizing Speed	保持时间 Duration																																				
0201,	1mm	<0.5mm/s	10±1s																																				
0402, 0603,	2mm																																						
0805,1206																																							
类型 Type	a	b	c																																				
0201	0.25	0.3	0.3																																				
0402	0.4	1.5	0.5																																				
0603	1.0	3.0	1.2																																				
0805	1.2	4.0	1.65																																				
1206	2.0	5.8	1.9																																				

振动 Vibration	IEC 60068-2-80	① 将晶片焊接在测试基板上（如右图所示的环氧玻璃布板）； Solder the chip to the testing jig (glass epoxy board shown in the left) using eutectic solder. ② 晶片以全振幅为 1.5mm 进行振动，频率范围为 10Hz ~55 Hz； The chip shall be subjected to a simple harmonic motion having total amplitude of 1.5mm, the frequency being varied uniformly between the approximate limits of 10 and 55 Hz. ③ 振动频率按 10Hz→55Hz→10Hz 循环，周期为 1 分钟，在空间三个互相垂直的方向上各振动 2 小时（共 6 小时）。 The frequency ranges from 10 to 55 Hz and return to 10 Hz shall be traversed in approximately 1 minute. This motion shall be applied for a period of 2 hours in each 3mutually perpendicular directions (total of 6 hours).	无外观损伤。 No visible damage. 铜箔 Cu pad 阻焊膜 Solder mask  环氧玻璃布板Glass Epoxy Board															
坠落 Dropping	IEC 60068-2-32	从 1m 的高度让晶片自由坠落至水泥地面 10 次。 Drop a chip 10 times on a concrete floor from a height of 1 meter.	无外观损伤。 No visible damage.															
可焊性 Solderability	IEC 60068-2-58	① 焊接温度 Solder temperature: 245±5℃. ② 浸渍时间 Duration: 3±0.3s. ③ 焊锡成分 Solder: 96.5Sn/3.0Ag/0.5Cu. ④ 助焊剂 Flux: （重量比）25%松香和 75%酒精 25% Resin and 75% ethanol in weight.	① 无外观损伤； No visible damage. ② 元件端电极的焊锡覆盖率不小于 95%。 Wetting shall exceed 95% coverage.															
耐焊性 Resistance to Soldering Heat	IEC 60068-2-58	① 焊接温度 Solder temperature: 260±5℃. ② 浸渍时间 Duration: 10±1s. ③ 焊锡成分 Solder: 96.5Sn/3.0Ag/0.5Cu. ④ 助焊剂 Flux: （重量比）25%松香和 75%酒精 25% Resin and 75% ethanol in weight. ⑤ 试验后标准条件下放置 1~2 小时后测量。 The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① 无外观损伤； No visible damage. ② ΔR25/R25 ≤2% ③ ΔB/B ≤1%															
温度周期 Temperature cycling	IEC 60068-2-14	① 无负载于下表所示的环境条件下重复 5 次。 5 cycles of following sequence without loading. <table><tr><td>步骤 Step</td><td>温度 Temperature</td><td>时间 Time</td></tr><tr><td>1</td><td>-40±5℃</td><td>30±3min</td></tr><tr><td>2</td><td>25±2℃</td><td>5±3min</td></tr><tr><td>3</td><td>125±2℃</td><td>30±3min</td></tr><tr><td>4</td><td>25±2℃</td><td>5±3min</td></tr></table> ② 试验后标准条件下放置 1~2 小时后测量。 The chip shall be stabilized at normal condition for 1~2 hours before measuring.	步骤 Step	温度 Temperature	时间 Time	1	-40±5℃	30±3min	2	25±2℃	5±3min	3	125±2℃	30±3min	4	25±2℃	5±3min	① 无外观损伤； No visible damage. ② ΔR25/R25 ≤2% ③ ΔB/B ≤1%
步骤 Step	温度 Temperature	时间 Time																
1	-40±5℃	30±3min																
2	25±2℃	5±3min																
3	125±2℃	30±3min																
4	25±2℃	5±3min																
高温存放 Resistance to dry heat	IEC 60068-2-2	① 在 125±5℃空气中，无负载放置 1000±24 小时。 125±5℃ in air, for 1000±24 hours without loading. ② 试验后标准条件下放置 1~2 小时后测量。 The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① 无外观损伤； No visible damage. ② ΔR25/R25 ≤2% ③ ΔB/B ≤1%															

低温存放 Resistance to cold	IEC 60068-2-1	① 在 $-40 \pm 3^{\circ}\text{C}$ 空气中, 无负载放置 1000 ± 24 小时。 $-40 \pm 3^{\circ}\text{C}$ in air, for 1000 ± 24 hours without loading. ② 试验后标准条件下放置 1~2 小时后测量。 The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① 无外观损伤; No visible damage. ② $ \Delta R_{25}/R_{25} \leq 2\%$ ③ $ \Delta B/B \leq 1\%$
湿热存放 Resistance to damp heat	IEC 60068-2-78	① 在 $60 \pm 2^{\circ}\text{C}$, 相对湿度 90~95% 空气中, 无负载放置 1000 ± 24 小时。 $60 \pm 2^{\circ}\text{C}$, 90~95%RH in air, for 1000 ± 24 hours without loading. ② 试验后标准条件下放置 1~2 小时后测量。 The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① 无外观损伤; No visible damage. ② $ \Delta R_{25}/R_{25} \leq 2\%$ ③ $ \Delta B/B \leq 1\%$
高温负荷 Resistance to high temperature load	IEC 60539-1 5.25.4	① 在 $85 \pm 2^{\circ}\text{C}$ 空气中, 施加允许工作电流 1000 ± 48 小时。 $85 \pm 2^{\circ}\text{C}$ in air with permissive operating current for 1000 ± 48 hours ② 试验后标准条件下放置 1~2 小时后测量。 The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① 无外观损伤; No visible damage. ② $ \Delta R_{25}/R_{25} \leq 2\%$ ③ $ \Delta B/B \leq 1\%$


7 编带 Taping

类型 Type	0201	0402	0603	0805	1206
编带厚度 Tape thickness(mm)	0.5 ± 0.15	0.5 ± 0.15	0.8 ± 0.15	0.85 ± 0.2	1.8 ± 0.2
编带材质 Tape material	纸带 Paper Tape				塑载带 Embossed Tape
每盘数量 Quantity per Reel	15K	10K	4K	4K	3K


(1) 纸带尺寸 Paper Tape Dimensions

(单位 Unit: mm)


QN0201 系列 QN0201 series




QN0402 系列 QN0402 series




QN0603 系列 QN0603 series



QN0805 系列 QN0805 series




(2) 塑载带尺寸 (单位: mm) Embossed Tape dimensions. (Unit: mm)




类型 Type	A0 (± 0.2)	B0 (± 0.2)	K0Max.	T Max.	W (± 0.3)	P0 (± 0.2)	P (± 0.2)	P2 (± 0.2)
1206	1.9	3.5	2.0	0.30	8.0	4.0	4.0	2.0

(3) 卷盘尺寸 Reel Dimensions(单位 Unit: mm)



(4) 塑带卷盘尺寸 Embossed Tape Reel Dimensions

(单位 Unit: mm)



类型 Type	规格 Spec.	尺寸 Dimensions(mm)		
		A	W	C
1206	7"	178±2	8.4+2.0/-0.0	58±2

8 储存

• 储存条件

- 储存温度: $-10^{\circ}\text{C} \sim 40^{\circ}\text{C}$
- 相对湿度: $\leq 75\% \text{RH}$
- 避免接触粉尘、腐蚀性气氛和阳光

• 储存期限: 产品交付后 6 个月

9 注意事项

• QN 系列热敏电阻不可在以下条件下工作或储存:

- 腐蚀性气体或还原性气体
(氯气、硫化氢气体、氨气、硫酸气体、一氧化氮等)。
- 挥发性或易燃性气体
- 多尘条件
- 高压或低压条件
- 潮湿场所
- 存在盐水、油、化学液体或有机溶剂的场所
- 强烈振动
- 存在类似有害条件的其他场所

• QN 系列热敏电阻的陶瓷属于易碎材料, 使用时不可施加过大压力或冲击。

• QN 系列热敏电阻不可在超过目录规定的温度范围情况下工作。

8 Storage

• Storage Conditions

- Storage Temperature: $-10^{\circ}\text{C} \sim 40^{\circ}\text{C}$
- Relative Humidity: $\leq 75\% \text{RH}$
- Keep away from corrosive atmosphere and sunlight.

• Period of Storage: 6 Months after delivery

9 Notes & Warnings

• The QN series thermistors shall not be operated and stored under the following environmental condition:

- Corrosive or deoxidized atmospheres
(such as chlorine, sulfurated hydrogen, ammonia, sulfuric acid, nitric oxide and so on)
- Volatile or inflammable atmospheres
- Dusty condition
- Excessive high or low pressure condition
- Humid site
- Places with brine, oil, chemical liquid or organic solvent
- Intense vibration
- Places with analogously deleterious conditions

• The ceramic body of the QN series thermistors is fragile, no excessive pressure or impact shall be exerted on it.

• The QN series thermistors shall not be operated beyond the specified "Operating Temperature Range" in the catalog.

10 建议焊接条件


• 回流焊

- 温升 1~2°C/sec.
- 预热: 150~190°C/90±30 sec.
- 大于 240°C时间: 20~40sec
- 峰值温度: 最高 260°C/10 sec.
- 焊锡: 96.5Sn/3.0Ag/0.5Cu
- 回流焊: 最多 2 次

10 Recommended Soldering Technologies

• Re-flowing Profile

- 1~2°C/sec. Ramp
- Pre-heating: 150~190°C/90±30 sec.
- Time above 240°C: 20~40 sec.
- Peak temperature: 260°C Max./10 sec.
- Solder paste: 96.5Sn/3.0Ag/0.5Cu
- Max.2 times for re-flowing.



• 手工焊


- 烙铁功率: 最大 30W
- 预热: 150°C/60 sec.
- 烙铁头温度: 最高 350°C
- 焊接时间: 最多 3sec.
- 焊锡: 96.5Sn/3.0Ag/0.5Cu
- 手工焊: 最多 1 次

[注: 不要使烙铁头接触到端头]

• Iron Soldering Profile

- Iron soldering power: Max.30W
- Pre-heating: 150°C/60 sec.
- Soldering Tip temperature: 350°C Max.
- Soldering time: 3 sec Max.
- Solder paste: 96.5Sn/3.0Ag/0.5Cu
- Max.1 times for iron soldering

[Note: Take care not to apply the tip of the soldering iron to the terminal electrodes.]



11 R-T 表 R-T table

QN1206X104J4250FB

温度 Temp. (°C)	R 最小值 R_Min (Kohm)	R 中心值 R_Cent (Kohm)	R 最大值 R_Max (Kohm)	阻值公差 Res TOL.	温度公差 Temp. TOL.(°C)
-40	4,022.168	4,397.119	4,795.007	9.05%	1.22
-39	3,746.551	4,092.874	4,460.031	8.97%	1.21
-38	3,491.669	3,811.717	4,150.698	8.89%	1.21
-37	3,255.828	3,551.749	3,864.879	8.82%	1.21
-36	3,037.483	3,311.236	3,600.637	8.74%	1.21
-35	2,835.225	3,088.599	3,356.205	8.66%	1.21
-34	2,647.767	2,882.396	3,129.972	8.59%	1.21
-33	2,473.931	2,691.310	2,920.469	8.51%	1.21
-32	2,312.643	2,514.137	2,726.353	8.44%	1.21
-31	2,162.918	2,349.778	2,546.398	8.37%	1.21
-30	2,023.855	2,197.225	2,379.483	8.29%	1.20
-29	1,894.628	2,055.558	2,224.581	8.22%	1.20
-28	1,774.481	1,923.932	2,080.754	8.15%	1.20
-27	1,662.720	1,801.573	1,947.142	8.08%	1.20
-26	1,558.707	1,687.773	1,822.957	8.01%	1.20
-25	1,461.859	1,581.881	1,707.476	7.94%	1.20
-24	1,371.457	1,483.100	1,599.821	7.87%	1.19
-23	1,287.219	1,391.113	1,499.634	7.80%	1.19
-22	1,208.687	1,305.413	1,406.354	7.73%	1.19
-21	1,135.441	1,225.531	1,319.462	7.66%	1.19
-20	1,067.092	1,151.037	1,238.481	7.60%	1.19
-19	1,003.284	1,081.535	1,162.975	7.53%	1.19
-18	943.687	1,016.661	1,092.540	7.46%	1.18
-17	887.999	956.080	1,026.806	7.40%	1.18
-16	835.941	899.481	965.431	7.33%	1.18
-15	787.253	846.579	908.099	7.27%	1.18
-14	741.698	797.111	854.522	7.20%	1.18
-13	699.056	750.834	804.431	7.14%	1.17
-12	659.124	707.524	757.579	7.07%	1.17
-11	621.714	666.972	713.737	7.01%	1.17
-10	586.651	628.988	672.695	6.95%	1.17
-9	553.727	593.342	634.202	6.89%	1.16
-8	522.849	559.931	598.143	6.82%	1.16
-7	493.879	528.602	564.351	6.76%	1.16
-6	466.687	499.212	532.669	6.70%	1.16
-5	441.155	471.632	502.954	6.64%	1.16
-4	417.201	445.772	475.109	6.58%	1.15
-3	394.687	421.480	448.966	6.52%	1.15
-2	373.518	398.652	424.414	6.46%	1.15
-1	353.607	377.193	401.345	6.40%	1.14
0	334.872	357.012	379.663	6.34%	1.14
1	317.219	338.006	359.255	6.29%	1.14
2	300.598	320.122	340.061	6.23%	1.14

温度 Temp. (°C)	R 最小值 R_Min (Kohm)	R 中心值 R_Cent (Kohm)	R 最大值 R_Max (Kohm)	阻值公差 Res TOL.	温度公差 Temp. TOL.(°C)
3	284.943	303.287	322.004	6.17%	1.13
4	270.194	287.434	305.009	6.11%	1.13
5	256.292	272.500	289.007	6.06%	1.13
6	243.185	258.426	273.936	6.00%	1.12
7	230.823	245.160	259.737	5.95%	1.12
8	219.158	232.649	246.353	5.89%	1.12
9	208.149	220.847	233.734	5.84%	1.12
10	197.754	209.710	221.832	5.78%	1.11
11	187.937	199.196	210.602	5.73%	1.11
12	178.661	189.268	200.003	5.67%	1.11
13	169.895	179.890	189.996	5.62%	1.10
14	161.607	171.028	180.545	5.57%	1.10
15	153.768	162.651	171.616	5.51%	1.10
16	146.350	154.726	163.173	5.46%	1.09
17	139.330	147.232	155.193	5.41%	1.09
18	132.686	140.142	147.647	5.35%	1.08
19	126.396	133.432	140.508	5.30%	1.08
20	120.437	127.080	133.754	5.25%	1.08
21	114.793	121.066	127.362	5.20%	1.07
22	109.443	115.368	121.310	5.15%	1.07
23	104.372	109.970	115.578	5.10%	1.07
24	99.562	104.852	110.147	5.05%	1.06
25	95.000	100.000	105.000	5.00%	1.06
26	90.586	95.398	100.215	5.05%	1.08
27	86.399	91.032	95.674	5.10%	1.09
28	82.429	86.889	91.362	5.15%	1.11
29	78.661	82.956	87.267	5.20%	1.13
30	75.085	79.222	83.377	5.24%	1.14
31	71.691	75.675	79.681	5.29%	1.16
32	68.468	72.306	76.168	5.34%	1.18
33	65.407	69.104	72.828	5.39%	1.20
34	62.498	66.061	69.652	5.44%	1.22
35	59.734	63.167	66.631	5.48%	1.23
36	57.106	60.415	63.756	5.53%	1.25
37	54.607	57.797	61.020	5.58%	1.27
38	52.230	55.306	58.416	5.62%	1.29
39	49.969	52.934	55.936	5.67%	1.31
40	47.817	50.677	53.573	5.72%	1.32
41	45.770	48.528	51.324	5.76%	1.34
42	43.821	46.482	49.181	5.81%	1.36
43	41.965	44.533	47.139	5.85%	1.38
44	40.197	42.675	45.191	5.90%	1.40
45	38.512	40.904	43.334	5.94%	1.42
46	36.905	39.213	41.561	5.99%	1.44
47	35.373	37.601	39.869	6.03%	1.46

温度 Temp. (°C)	R 最小值 R_Min (Kohm)	R 中心值 R_Cent (Kohm)	R 最大值 R_Max (Kohm)	阻值公差 Res TOL.	温度公差 Temp. TOL.(°C)
48	33.912	36.063	38.254	6.08%	1.48
49	32.519	34.595	36.713	6.12%	1.50
50	31.189	33.195	35.241	6.16%	1.51
51	29.922	31.859	33.837	6.21%	1.53
52	28.713	30.584	32.496	6.25%	1.55
53	27.558	29.366	31.214	6.29%	1.57
54	26.455	28.203	29.990	6.34%	1.59
55	25.402	27.091	28.819	6.38%	1.61
56	24.396	26.028	27.700	6.42%	1.63
57	23.435	25.013	26.630	6.47%	1.65
58	22.516	24.042	25.606	6.51%	1.67
59	21.638	23.113	24.627	6.55%	1.69
60	20.798	22.224	23.689	6.59%	1.71
61	19.995	21.374	22.792	6.63%	1.73
62	19.226	20.561	21.933	6.67%	1.75
63	18.491	19.782	21.110	6.72%	1.78
64	17.787	19.036	20.323	6.76%	1.80
65	17.113	18.323	19.568	6.80%	1.82
66	16.470	17.640	18.846	6.84%	1.84
67	15.854	16.986	18.155	6.88%	1.86
68	15.263	16.360	17.492	6.92%	1.88
69	14.698	15.760	16.856	6.96%	1.90
70	14.156	15.184	16.247	7.00%	1.92
71	13.635	14.631	15.661	7.04%	1.94
72	13.136	14.101	15.099	7.08%	1.97
73	12.657	13.592	14.559	7.12%	1.99
74	12.198	13.104	14.041	7.16%	2.01
75	11.758	12.635	13.544	7.19%	2.03
76	11.337	12.187	13.069	7.23%	2.05
77	10.932	11.757	12.612	7.27%	2.07
78	10.544	11.344	12.173	7.31%	2.10
79	10.172	10.947	11.751	7.35%	2.12
80	9.814	10.566	11.346	7.39%	2.14
81	9.471	10.200	10.957	7.42%	2.16
82	9.141	9.848	10.583	7.46%	2.19
83	8.824	9.510	10.223	7.50%	2.21
84	8.520	9.185	9.877	7.54%	2.23
85	8.227	8.873	9.545	7.57%	2.25
86	7.946	8.572	9.225	7.61%	2.28
87	7.676	8.283	8.917	7.65%	2.30
88	7.416	8.006	8.621	7.69%	2.32
89	7.166	7.738	8.336	7.72%	2.35
90	6.925	7.481	8.061	7.76%	2.37
91	6.695	7.234	7.798	7.79%	2.39
92	6.473	6.997	7.545	7.83%	2.42

温度 Temp. (°C)	R 最小值 R_Min (Kohm)	R 中心值 R_Cent (Kohm)	R 最大值 R_Max (Kohm)	阻值公差 Res TOL.	温度公差 Temp. TOL.(°C)
93	6.259	6.769	7.301	7.87%	2.44
94	6.054	6.548	7.066	7.90%	2.46
95	5.856	6.337	6.839	7.94%	2.49
96	5.665	6.132	6.620	7.97%	2.51
97	5.480	5.934	6.409	8.01%	2.53
98	5.303	5.744	6.206	8.04%	2.56
99	5.132	5.561	6.010	8.08%	2.58
100	4.967	5.384	5.821	8.11%	2.61
101	4.809	5.214	5.639	8.15%	2.63
102	4.657	5.051	5.464	8.18%	2.66
103	4.510	4.893	5.295	8.22%	2.68
104	4.369	4.741	5.132	8.25%	2.70
105	4.232	4.594	4.975	8.28%	2.73
106	4.100	4.453	4.823	8.32%	2.75
107	3.973	4.316	4.677	8.35%	2.78
108	3.851	4.184	4.535	8.39%	2.80
109	3.733	4.057	4.399	8.42%	2.83
110	3.619	3.934	4.267	8.45%	2.85
111	3.508	3.816	4.139	8.49%	2.88
112	3.402	3.701	4.016	8.52%	2.90
113	3.299	3.591	3.898	8.55%	2.93
114	3.200	3.484	3.783	8.58%	2.96
115	3.104	3.380	3.672	8.62%	2.98
116	3.012	3.281	3.565	8.65%	3.01
117	2.924	3.185	3.462	8.68%	3.03
118	2.838	3.093	3.362	8.71%	3.06
119	2.755	3.003	3.266	8.75%	3.08
120	2.674	2.916	3.172	8.78%	3.11
121	2.596	2.832	3.082	8.81%	3.14
122	2.521	2.751	2.994	8.84%	3.16
123	2.448	2.672	2.909	8.87%	3.19
124	2.378	2.596	2.827	8.90%	3.22
125	2.309	2.522	2.747	8.94%	3.24