

SuperMOS – SOT-23-3L -30V BV_{DSS} , 42m Ω $R_{DS(on)}$, P-channel MOSFET

1. Description

The AO3401A is P-Channel enhancement MOS Field Effect Transistor. Uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge. Device is suitable for use in DC-DC conversion, power switch and charging circuit. Standard Product AO3401A is Pb-free.

2. Features

- 30V, $R_{DS(on)}$ =42m Ω (TYP.) @ V_{GS} =-10V
 $R_{DS(on)}$ =49m Ω (TYP.) @ V_{GS} =-4.5V
 $R_{DS(on)}$ =72m Ω (TYP.) @ V_{GS} =-2.5V
- Fast Switching
- High density cell design for low $R_{DS(on)}$
- Material: Halogen free
- Reliable and rugged
- Avalanche Rated
- Low leakage current



3. Applications

- PWM applications
- Load switch
- Power management in portable/desktop PCs
- DC/DC conversion

4. Ordering Information

Part Number	Package	Marking	Material	Packing	Quantity per reel	Flammability Rating	Reel Size
AO3401A	SOT-23-3L	3401	Halogen free	Tape & Reel	3,000 PCS	UL 94V-0	7 inches

5. Pin Configuration and Functions

Pin	Function	Outline	Circuit Diagram
1	Gate		
2	Source		
3	Drain		

6. Specification

Absolute Maximum Rating & Thermal Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		BV_{DSS}	-30	V
Gate-Source Voltage		V_{GS}	± 12	V
Continuous Drain Current	$T_A=25^{\circ}\text{C}$	I_D	-3.9	A
	$T_A=100^{\circ}\text{C}$		-2.4	
Maximum Power Dissipation	$T_A=25^{\circ}\text{C}$	P_D	1.5	W
Pulsed Drain Current ^a		I_{DM}	-15.6	A
Junction-to-Ambient Thermal Resistance ^b		$R_{\theta JA}$	83	$^{\circ}\text{C/W}$
Operating Junction Temperature		T_J	-55 to +150	$^{\circ}\text{C}$
Storage Temperature Range		T_{stg}	-55 to +150	$^{\circ}\text{C}$

Note:

a: Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature.

b: $R_{\theta JA}$ is measured with the device mounted on a 1inch² pad of 2oz copper FR4 PCB.

c: Pulse Test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 0.5\%$.

AO3401A

Rev-1.1


Electrical Characteristics

At TA = 25°C unless otherwise specified

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =-250uA	-30			V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-30V, V _{GS} =0V			-1	uA
Gate-to-source Leakage Current	I _{GSS}	V _{DS} =0V, V _{GS} =±12V			±100	nA
ON CHARACTERISTICS						
Gate Threshold Voltage	V _{GS(TH)}	V _{GS} =V _{DS} , I _D =-250uA	-0.5	-0.9	-1.1	V
Drain-to-source On-resistance °	R _{DS(on)}	V _{GS} =-10V, I _D =-3.9A		42	58	mΩ
		V _{GS} =-4.5V, I _D =-3.5A		49	65	
		V _{GS} =-2.5V, I _D =-2.5A		72	90	
CHARGES, CAPACITANCES AND GATE RESISTANCE						
Input Capacitance	C _{ISS}	V _{GS} =0V, V _{DS} =-15V f=1MHz		510		pF
Output Capacitance	C _{OSS}			54		
Reverse Transfer Capacitance	C _{RSS}			47		
Total Gate Charge	Q _{G(TOT)}	V _{GS} =0 to -4.5V V _{DS} =-15V, I _D =-3A		6		nC
Gate-to-Source Charge	Q _{GS}			1.4		
Gate-to-Drain Charge	Q _{GD}			2		
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	t _{d(ON)}	V _{GS} =-4.5V, V _{DS} =-15V I _D =-3A, R _G =3Ω		10		ns
Rise Time	t _r			80		
Turn-Off Delay Time	t _{d(OFF)}			120		
Fall Time	t _f			350		
BODY DIODE CHARACTERISTICS						
Forward Voltage	V _{SD}	V _{GS} =0V, I _S =-2A			-1.2	V


7. Dimension (SOT-23-3L)

POD(Z)



COMMON DIMENSIONS CUNITS MEASURE=MILLIMETER					
SYMBOL	MIN	MAX	SYMBOL	MIN	MAX
A	1.00	1.30	D	2.70	3.10
A1	0.00	0.11	E	2.60	3.00
A2	1.00	1.25	E1	1.50	1.80
b	0.30	0.50	e	1.70	2.10
c	0.10	0.25	L	0.30	0.55
L1	0.55	0.70			

8. Recommended Soldering Footprint



DISCLAIMER

ELECSUPER PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with ElecSuper products. You are solely responsible for

(1) selecting the appropriate ElecSuper products for your application;

(2) designing, validating and testing your application;

(3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. ElecSuper grants you permission to use these resources only for development of an application that uses the ElecSuper products described in the resource. Other reproduction and display of these resources are prohibited. No license is granted to any other ElecSuper intellectual property right or to any third party intellectual property right. ElecSuper disclaims responsibility for, and you will fully indemnify ElecSuper and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources. ElecSuper's products are provided subject to ElecSuper's Terms of Sale or other applicable terms available either on www.elecsuper.com or provided in conjunction with such ElecSuper products. ElecSuper's provision of these resources does not expand or otherwise alter ElecSuper's applicable warranties or warranty disclaimers for ElecSuper products.