










P.C.B LAND DIMENSION




SW电路图



Unless otherwise specified, Tolerance:
 X. ±0.30
 X.x ±0.20
 X.xx ±0.15
 X.xxx ±0.10
 Angles ±3°

G-Switch Electronic (HongKong) CO.,Ltd.

DESIGN FengFengChen	DATE 2019.05.29	Molde code:
CHECKED	DATE	GT-TC044X-HXXXX-LX
APPROVED	DATE	
http://www.dg-switch.com	REV.: X1	SCALE: 4:1
TEL:0769-82388879	SIZE: A4	SHEET: 1/1



GT-TC044X-HXXXX-LX

G-SWITCH

Operating Force
 A=160gf
 B=200gf

Switch Height (mm)
 H0155=1.55mm

Switch lifetime (Force)
 L1=100,000 Cycles

G-Switch Specification:

Operating temperature range : -30°Cto+85°C
 Rating : 50mA.12V DC
 Insulation resistance: : 100MΩ min.100V DC
 Dielectric strength : 250V AC for 1 min
 Contact resistance: : 100m Ω max.
 Travel:0.15±0.05mm