


GT-TC191X-H026-L60



G-Switch

Operating Force


A=160gf
B=220gf

Switch Height
H026=2.6mm

Switch Lifetime
L60=6,000,000 Cycles




RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05



CIRCUIT DIAGRAM

5	COVER	STAINLESS STEEL	Au PLATING
4	BUTTON	HIGH TEMPERATURE PLASTIC	BLACK
3	CONTACT	STAINLESS STEEL	Ag PLATING
2	TERMINAL	COPPER ALLOY	Ag PLATING
1	BASE	HIGH TEMPERATURE PLASTIC	BLACK
NO.	PART NAME	MATERIAL	REMARK



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
30 < L ±0.30
10 < L ≤ 30 ±0.20
5 < L ≤ 10 ±0.15
30 ≤ 5 ±0.10
X° ±2°

Title: Horizontal Tact Switch
Mid-Mout 0.60 SMT 4.5×2.2×H2.6mm

Molde Code: GT-TC191X-H026-L60

DRAWN	CHECKED	APPROVED	DATE
Jiang	Xia	Chen	2023.02.01

品赞科技®
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1