





UMAX7101201
SFP CAGE



KSP20LG154
SFP CONNECTOR

MATERIAL (RoHS COMPLIANT):


CAGE:
COPPER ALLOY


PLATING:(SEE PART NUMBER FOR OPTION)
OPTION1:100μ" [2.54 μm] MIN. BRIGHT TIN PLATING OVER 50 μ" (1.27 μm) MIN. NICKEL UNDER PLATING. (BRIGHT TIN SOLDER TEMPERATURE 230°C MAX.).
OPTION3: 100μ" [2.54 μm] MIN. MATTE TIN PLATING OVER 50 μ" (1.27 μm) MIN. NICKEL UNDER PLATING.(MATTE TIN SOLDER TEMPRETURE 245°C MAX. IN 10 SECONDS OF PEAK TIME,)


DUST COVER
THERMOPLASTIC, COLOR BLACK.


PACKAGING:
TAPE AND REEL OR TRAY PACKAGING.

TEMPERATURE RANGE:
-40°C TO +85°C

				TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: SFP CAGE 1x1 NICKEL PLATING Through Hole-Solder				
				LINEAR	ANGLES							
				X,±0.40	X°,± 3°							
				.X±0.30	.X°±							
						APPD: Jason	MAT'L:	PART NO. UMAX7101X01				
A0	-----	Johnny	Jun,09,2025	.XX±0.20	.XX°±	CHKD: Schumi	FINISH:	DWG NO. C-UMAX7D1018				
REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX°±	DRWN:Lei Songping	Q'TY:		UNITS MM	SCALE 1 : 1	SHEET 1 OF 4	REV A0







RECOMMENDED SFP HOST BOARD LAYOUT
(ONE SIDE CAGE MOUNTING)
(SCALE 4:1)

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: SFP CAGE 1x1 NICKEL PLATING Through Hole-Solder				
LINEAR	ANGLES			PART NO. UMAX7101X01				
X±0.40	X°± 3°			DWG NO. C-UMAX7D1018				
.X±0.30	.X°±	APPD: Jason	MAT'L:		UNITS	SCALE	SHEET	REV
.XX±0.20	.XX°±	CHKD: Schumi	FINISH:		MM	1 : 1	4 OF 4	A0
.XXX±0.10	.XXX°±	DRWN:Lei Songping	Q'TY:					

REV	ECN NO.	NAME	DATE
	SEE SHEE 1		