


LMUN5111T1G


Bias Resistor Transistor

PNP Silicon Surface Mount Transistor
with Monolithic Bias Resistor Network



1. FEATURES

- Simplifies circuit design
- Reduces board space and component count
- The SC-70/SOT-323 package can be soldered using wave or reflow.
- The modified gull-winged leads absorb thermal stress during soldering eliminating the possibility of damage to the die.
- We declare that the material of product compliance with RoHS requirements and Halogen Free.



2. DEVICE MARKING AND RESISTOR VALUES

Device	Marking	R1(K)	R2(K)	Vin(V)	Shipping
LMUN5111T1G	6A	10	10	-40~+10	3000/Tape&Reel
LMUN5111T3G	6A	10	10	-40~+10	13000/Tape&Reel

3. MAXIMUM RATINGS(Ta = 25°C)

Parameter	Symbol	Limits	Unit
Collector-Emitter Voltage	VCEO	-50	V
Collector-Base Voltage	VCBO	-50	V
Collector Current — Continuous	IC	-100	mA

4. THERMAL CHARACTERISTICS

Parameter	Symbol	Limits	Unit
Total Device Dissipation, FR-5 Board (Note 1) @ TA = 25°C Derate above 25°C	PD	202 1.6	mW mW/°C
Thermal Resistance, Junction-to-Ambient(Note 1)	RθJA	618	°C/W
Junction and Storage temperature	TJ,Tstg	-55~+150	°C

1. FR-5 @ Minimum Pad.

5. ELECTRICAL CHARACTERISTICS (Ta= 25°C)

OFF CHARACTERISTICS





Characteristic	Symbol	Min.	Typ.	Max.	Unit
Collector–Emitter Breakdown Voltage (IC = -2.0 mA, IB = 0)	VBR(CEO)	-50	-	-	V
Collector–Base Breakdown Voltage (IC = -10 μ A, IE = 0)	VBR(CBO)	-50	-	-	V
Collector-Base Cutoff Current (VCB = -50 V, IE = 0)	ICBO	-	-	-100	nA
Collector-Emitter Cutoff Current (VCE = -50 V, IB = 0)	ICEO	-	-	-500	nA
Emitter-Base Cutoff Current (VEB = -6.0 V, IC = 0)	IEBO	-	-	-0.5	mA

ON CHARACTERISTICS (Note 2.)


DC Current Gain (IC = -5.0 mA, VCE = -10 V)	HFE	35	60	250	
Collector–Emitter Saturation Voltage (IC = -10 mA, IB = -0.3 mA)	VCE(sat)	-	-	-0.25	V
Input Voltage(on) (VCE = -0.3V, IC = -10mA)	VIN(on)	-3	-	-	V
Input Voltage(off) (VCE = -5V, IC = -100 μ A)	VIN(off)	-	-	-0.5	V
Output Voltage (on) (VCC = -5.0 V, VB = -2.5 V, RL = 1.0K Ω)	VOL	-	-	-0.2	V
Output Voltage (on) (VCC = -5.0 V, VB = -0.5 V, RL = 1.0K Ω)	VOH	-4.9	-	-	V
Input Resistor	R1	7	10	13	K Ω
Resistor Ratio	R1/R2	0.8	1	1.2	

2. Pulse Test: Pulse Width < 300 μ s, Duty Cycle < 2.0%


6. ELECTRICAL CHARACTERISTICS CURVES



6. ELECTRICAL CHARACTERISTICS CURVES(Con.)




7.OUTLINE AND DIMENSIONS



SC70			
DIM	MIN	NOR	MAX
A	0.80	0.95	1.00
A1	0.00	0.05	0.10
A2	0.7 REF		
b	0.30	0.35	0.40
c	0.10	0.15	0.25
D	1.80	2.05	2.20
E	1.15	1.30	1.35
e	1.20	1.30	1.40
e1	0.65 BSC		
L	0.20	0.35	0.56
He	2.00	2.10	2.40
ALL Dimension in mm			

8.SOLDERING FOOTPRINT



SC70	
DIM	MIN
A	1.90
B	0.65
C	0.65
X	0.70
Y	0.90

DISCLAIMER

- Curve guarantee in the specification. The curve of test items with electric parameter is used as quality guarantee. The curve of test items without electric parameter is used as reference only.
- Before you use our Products for new Project, you are requested to carefully read this document and fully understand its contents. LRC shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any LRC's Products against warning, caution or note contained in this document.
- All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using LRC's Products, please confirm the latest information with a LRC sales representative.