

SPECIFICATIONS





Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
PH2.0-02-01PWS-R	2*1	0.00	2.00
PH2.0-02-02PWS-R	2*2	2.00	4.00
PH2.0-02-03PWS-R	2*3	4.00	6.00
PH2.0-02-04PWS-R	2*4	6.00	8.00
PH2.0-02-05PWS-R	2*5	8.00	10.00
PH2.0-02-06PWS-R	2*6	10.00	12.00
PH2.0-02-07PWS-R	2*7	12.00	14.00
PH2.0-02-08PWS-R	2*8	14.00	16.00
PH2.0-02-09PWS-R	2*9	16.00	18.00
.....			
PH2.0-02-40PWS-R	2*40	(PIN-1)x2.0	(PIN)x2.0

PART NUMBER DESCRIPTION:

PH2.0-02-NPWS-R

(R=编带)
(D=单排; S=双排)
(Z=直脚; W=弯脚)
(PIN数量; 01.....40PIN)
(排针开关)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 2.0PH H2.0 2xPin SMT PC6.5 PA3.8 PB2.5 L8.0 6T	
DECIMALS:	ANGLES:	PAR	PH2.0-02-NPWS-R
X.±0.30	X°±5'	DWN	
X.X±0.25	X.X°±1'	CHKD	
X.XX±0.20	X.XX°±0.5'	APVD	
CUSTOMER COPY		SCALE N:A	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A