

ACT Series

Features

- High common mode impedance at high frequency effects excellent noise suppression performance.
- Support a wide range of $-40 \sim +105^{\circ}\text{C}$, can be used for high temperature resistant vehicle equipment.
- High precision automatic winding method ensures high stability and reliability.
- The products 100% Lead(Pb) and RoHS compliant.
- Halogen Free.


Applications

- The ACT series can be used as a common mode filter for vehicle LAN system such as CAN BUS and FlexRay.

Test Equipment and Conditions

- All test data is referenced to 25°C ambient.
 - Operating temperature range -40°C to $+105^{\circ}\text{C}$. (Including self - temperature rise).
 - The part temperature (ambient + temp rise) should not exceed 105°C under worst case operating conditions.
- Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature, part temperature should be verified in the end application.

External Dimensions (Unit:mm)



TYPE	A	B	C	D1 typ	D2 typ	a typ	b typ	c typ	d typ	Q'TY/Reel
ACT3225	3.2±0.2	2.5±0.2	2.2±0.2	0.75	0.9	2	3.7	0.6	2.5	1000
ACT4532	4.5±0.2	3.2±0.2	2.8±0.2	1	1.2	2.5	4.8	0.7	3.8	500


2. Part Number Code

ACT	3225	R	110	W2
Series Name	Dimensions: L*W*H	Tolerance	Inductance	Internal Controls

ACT Series

Part Number	Common Mode Impedance @10MHz		Common Mode Inductance @100KHz/0.1V	DC Resistance	Heating Rating Current	Rated Voltage	Withstanding Voltage Vode.	Insulation Resistance
	(Ω)Min.	(Ω)Typ.	(μH)+50%/-30%	(mΩ)Max.	(mA)Max.	(V)Max.	(V)Max.	(MΩ)Min
ACT3225R110-W2	300	550	11	400	300	50	125	10
ACT3225R220-W2	500	1100	22	500	250	50	125	10
ACT3225R510-W2	1000	2600	51	700	200	50	125	10
ACT3225R101-W2	2200	5100	100	1500	150	50	125	10
ACT3225R201-W2	5000	11000	200	5800	70	50	125	10
ACT4532R110-W2	300	600	11	600	250	50	125	10
ACT4532R220-W2	500	1200	22	1000	200	50	125	10
ACT4532R510-W2	1000	2800	51	1000	200	50	125	10
ACT4532R101-W2	2000	5800	100	2000	150	50	125	10
ACT4532R201-W2	5000	11000	200	4500	100	50	125	10

Characteristics(Reference)



Characteristics(Reference)

