








ROHS



NO.	DESCRIPTION	QTY	MATERIAL	PLATING
⑥	Washer	1	Spring steel	Sn-Plating
⑤	Nut	1	H59 BRASS	Ag-Plating
④	Tip spring	1	Bronze C5191 t=0.2	Ag-Plating
③	PIN	1	H59 BRASS	Ag-Plating
②	Housing	1	PBT	Black
①	Bushing	1	H59 BRASS	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	—	—	NEW	—	—	—



SPECIFICATION

- Rating : DC 20V 15A;
- Contact resistance: $\leq 30m\Omega$;
- Insulation resistance: $\geq 100M\Omega$ (DC250V);
- Withstand voltage: 500VAC ;
- Insertion and extraction force: 3-20N;
- life test: 5,000 cycles.

APPROVALS		DATE	浙江创都电子科技有限公司		
DRAWN		2020.11.20			
CHECKED			TITLE:	DC JACK	
APPROVALS			PART NO.	DC-1250M-15A-2.5	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
	10~30	±0.20			PROJ:
	5~10	±0.15			
	~ 5	±0.10	±2°	DRAWING NO.	—
SHEET 1 OF 1					