







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
PH2.54-02-01PWS-R	2*1	0.00	2.54
PH2.54-02-02PWS-R	2*2	2.54	5.08
PH2.54-02-03PWS-R	2*3	5.08	7.62
PH2.54-02-04PWS-R	2*4	7.62	10.16
PH2.54-02-05PWS-R	2*5	10.16	12.70
PH2.54-02-06PWS-R	2*6	12.70	15.24
PH2.54-02-07PWS-R	2*7	15.24	17.78
PH2.54-02-08PWS-R	2*8	17.78	20.32
PH2.54-02-09PWS-R	2*9	20.32	22.86
.....			
PH2.54-02-40PWS-R	2*40	(PIN-1)X2.54	(PIN)X2.54

PART NUMBER DESCRIPTION:

PH2.54-02-NPWS-R

(R=编带)
(D=单排; S=双排)
(Z=直脚; W=弯脚)
(PIN数量; 01.....40PIN)
(排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.54PH H2.5 2xnPin SMT PC7.5 PA6.0 PB3.2 L11.0 6T
			PAR PH2.54-02-NPWS-R
			DWN
			CHKD
DECIMALS:	ANGLES:		APVD
X.±0.30	X°±5'		SCALE N:A
X.X±0.20	X.X°±1'		UNIT:MM
X.XX±0.10	X.XX°±0.5'		SIZE:A4
CUSTOMER COPY		SHEET:1F1	
		REV:A	