

PDFN3030 Plastic-Encapsulate MOSFETS

Features

- $V_{DS}=-40V$
- $I_D=-49A$
- $R_{DS(on)}@V_{GS}=-10V < 13m\Omega$
- $R_{DS(on)}@V_{GS}=-4.5V < 18m\Omega$
- Trench Power LV MOSFET technology
- Voltage controlled small signal switch
- Fast Switching Speedze


Applications

- Power switching application
- Load switch
- Power management

Mechanical Data


- Case: PDFN3030
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Drain-source Voltage
-40 V
Drain Current
-49 Ampere

PDFN3030



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
PDFN3030	R3	0.0218	5000	10000	80000	13"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	-40
Gate-source Voltage	V_{GS}	V	± 20
Drain Current	I_D	A	-49
Pulsed Drain Current ⁽¹⁾	I_{DM}	A	-196
Total Power Dissipation	P_D	W	43
Single pulse avalanche energy ⁽²⁾	EAS	mJ	182
Junction temperature	T_J	°C	-55 ~+150
Storage temperature	T_{stg}	°C	-55 ~+150
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	°C / W	2.9

HD304P130S

P-CHANNEL MOSFET

● Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D =-250μA	V	-40	—	—
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-40V, V _{GS} =0V	μA	—	—	-1.0
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} =0V	nA	—	—	±100
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D =-250μA	V	-1.1	-1.6	-2.2
Static Drain-Source On-Resistance ⁽³⁾	R _{DS(ON)}	V _{GS} = -10V, I _D =-15A	mΩ	—	10.3	13
		V _{GS} = -4.5V, I _D =-10A		—	15	18

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C _{iss}	V _{DS} =-20V, V _{GS} =0V, f=1MHZ	pF	—	3360	—
Output Capacitance	C _{oss}			—	310	—
Reverse Transfer Capacitance	C _{rss}			—	230	—

● Switching Parameters







PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	t _{D(on)}	V _{GS} =-10V, V _{DD} =-20V, I _D =-15A, R _{GEN} =2.7Ω	nS	—	7	—
Turn-on Rise Time	t _r		nS	—	34	—
Turn-off Delay Time	t _{D(off)}		nS	—	127	—
Turn-off fall Time	t _f		nS	—	45	—
Total Gate Charge	Q _g	V _{DS} =-20V, I _D =-15A V _{GS} =-10V	nC	—	55	—
Gate-Source Charge	Q _{gs}		nC	—	10	—
Gate-Drain Charge	Q _{gd}		nC	—	8.8	—

● Drian-Source Diode Characteristics






PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V _{SD}	I _S =-15A, V _{GS} =0V	V	—	—	-1.0
Maximum Body-Diode Continuous Current	I _S	—	A	—	—	-49
Reverse recovery time	T _{rr}	V _{DD} =-20V I _S =-15A, V _{GS} =0V	nS	—	18	—
Reverse recovery charge	Q _{rr}	di/dt=-100A/μs	nC	—	10	—

Note :
(1)Repetitive Rating: Pulse width limited by maximum junction temperature.
(2)EAS condition : Tj=25°C ,VDD=-50V,VG=-10V,L=0.5mH,IAS=-27A,Rg=25Ω.
(3)Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● **Ratings And Characteristics Curves** ($T_a=25^\circ\text{C}$ Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (PDFN3030)



● Suggested Pad Layout




1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

