







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ2.54-2-1PUW	2*1	0.00	2.54
BX-PZ2.54-2-2PUW	2*2	2.54	5.08
BX-PZ2.54-2-3PUW	2*3	5.08	7.62
BX-PZ2.54-2-4PUW	2*4	7.62	10.16
BX-PZ2.54-2-5PUW	2*5	10.16	12.70
BX-PZ2.54-2-6PUW	2*6	12.70	15.24
BX-PZ2.54-2-7PUW	2*7	15.24	17.78
BX-PZ2.54-2-8PUW	2*8	17.78	20.32
BX-PZ2.54-2-9PUW	2*9	20.32	22.86
.....			
BX-PZ2.54-2-40PUW	2*40	(PIN-1)X2.54	(PIN)X2.54



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	Yu			料号 PART NO.	BX-PZ2.54-2-NPUW		版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	HUANG			品名 TITLE	2.54PH H2.5 2xnPin SMT PC7.5 PA6.0 PB3.2 L11.0 6T		页次 SHEET	1/1
			X.±0.30	X°±5°	核准 APPROVAL	RUAN			客户料号 CUTM.NO.				
			X.X±0.20	X.X°±1°		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			
			X.XX±0.10	X.XX°±0.5°									