




Surface Mount Superfast Recovery Rectifier

Reverse Voltage – 50 to 600 V

Forward Current –2 A

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Superfast reverse recovery time
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SMA
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.055g / 0.002oz

Absolute Maximum Ratings and Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.


Parameter	Symbols	ES2A	ES2B	ES2C	ES2D	ES2E	ES2G	ES2J	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	50	100	150	200	300	400	600	V
Maximum RMS voltage	V_{RMS}	35	70	105	140	210	280	420	V
Maximum DC Blocking Voltage	V_{DC}	50	100	150	200	300	400	600	V
Maximum Average Forward Rectified Current at $T_c=125\text{ }^{\circ}\text{C}$	$I_{\text{F(AV)}}$	2							A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	I_{FSM}	50							A
Maximum Forward Voltage at 2 A	V_{F}	1				1.25		1.68	V
Maximum DC Reverse Current at Rated DC Blocking Voltage $T_a=25\text{ }^{\circ}\text{C}$ $T_a=125\text{ }^{\circ}\text{C}$	I_{R}	5 100							μA
Typical Junction Capacitance at $V_{\text{R}}=4\text{V}$, $f=1\text{MHz}$	C_{j}	40							pF
Maximum Reverse Recovery Time ⁽¹⁾	t_{rr}	35							ns
Typical Thermal Resistance ⁽²⁾	$R_{\theta\text{JA}}$	60							$^{\circ}\text{C/W}$
Operating and Storage Temperature Range	T_{j} , T_{stg}	-55 ~ +150							$^{\circ}\text{C}$

(1) Measured with $I_F = 0.5\text{ A}$, $I_R = 1\text{ A}$, $t_{rr} = 0.25\text{ A}$.

(2) P.C.B. mounted with 1.0 X 1.0" (2.54 X 2.54 cm) copper pad areas.



Fig.1 Reverse Recovery Time Characteristic And Test Circuit Diagram



Note: 1. Rise Time = 7ns, max.
Input Impedance = 1megohm, 22pF.
2. Rise Time = 10ns, max.
Source Impedance = 50 ohms.




Fig.2 Maximum Average Forward Current Rating




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics




Fig.5 Typical Junction Capacitance






Fig.6 Maximum Non-Repetitive Peak Forward Surge Current




**PACKAGE OUTLINE**

Plastic surface mounted package; 2 leads

SMA



UNIT		A	D	E	B	c	e	g	b	a
mm	max	2.2	4.5	2.8	5.3	0.31	1.6	1.5	0.2	0.3
	min	1.9	4.0	2.4	4.8	0.15	1.3	0.9	0.05	
mil	max	87	181	110	209	12	63	59	7.9	12
	min	75	157	94	189	6	51	35	2	

The recommended mounting pad size**Marking**

Type number	Marking code
ES2A	ES2A
ES2B	ES2B
ES2C	ES2C
ES2D	ES2D
ES2E	ES2E
ES2G	ES2G
ES2J	ES2J