

SPECIFICATIONS

Current Rating: 1.0 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:-40°to+105°

Insulator Material:Polyester(UL94V-0)





Contact Material:Phosphor bronze

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
PM1.27-UL2D-1A	1	0.00	1.27
PM1.27-UL2D-2A	2	1.27	2.54
PM1.27-UL2D-3A	3	2.54	3.81
PM1.27-UL2D-4A	4	3.81	5.08
PM1.27-UL2D-5A	5	5.08	6.35
PM1.27-UL2D-6A	6	6.35	7.62
PM1.27-UL2D-7A	7	7.62	8.89
PM1.27-UL2D-8A	8	8.89	10.16
PM1.27-UL2D-9A	9	10.16	11.43
.....			
PM1.27-UL2D-50A	50	(PIN-1)x1.27	(PIN)x1.27

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.50	X.*± 5°	APR. Alex	TITLE: 11.27FH H4.3 1xNPin SMT W2.1 U 3 PC3.5 PB4.6 6T (左前右后)	
.XX±0.20	.X.*± 3°	CHK. Jack	DWG NO. PM1.27-UL2D-NA	
.XXX±0.10	.XX.*± 1°	DRA. Can	PROJ.	CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/3 REV. A