


**-30V/-60A P-Channel Advanced Power MOSFET****Features**

- Improved dv/dt Capability, High Ruggedness.
- Maximum Junction Temperature Range (150°C)
- 100% Avalanche Tested

BVDSS	-30	V
ID	-60	A
RDSON@VGS=-10V	5.8	mΩ
RDSON@VGS=-4.5V	9	mΩ

Applications

- PWM applications
- Load switch
- Power management

**Order Information**

Product	Package	Marking	Reel Size	Reel	Carton
PTD60P03	TO-252	PTD60P03	13inch	2500PCS	50000PCS

Absolute Maximum Ratings







Symbol	Parameter		Rating	Unit
Common Ratings (TC=25°C Unless Otherwise Noted)				
V _{(BR)DSS}	Drain-Source Breakdown Voltage		-30	V
V _{GS}	Gate-Source Voltage		±20	V
T _J	Maximum Junction Temperature		150	°C
T _{STG}	Storage Temperature Range		-55 to 150	°C
I _S	Diode Continuous Forward Current	TC =25°C	-60	A
Mounted on Large Heat Sink				
E _{AS}	Single Pulse Avalanche Energy (Note1)		144	mJ
I _{DM}	Pulse Drain Current Tested (Note2)	TC =25°C	-240	A
I _D	Continuous Drain current	TC =25°C	-60	A
P _D	Maximum Power Dissipation	TC =25°C	51	W
R _{θJC}	Thermal Resistance Junction-to-Case		2.45	°C/W

**-30V/-60A P-Channel Advanced Power MOSFET**

Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
V _{(BR)DSS}	Drain- Source Breakdown Voltage	VGS=0V ID=-250μA	-30	--	--	V
I _{DSS}	Zero Gate Voltage Drain current	VDS=-30V,VGS=0V	--	--	-1	μA
I _{GSS}	Gate-Body Leakage Current	VGS=±20V,VDS=0V	--	--	±100	nA
V _{GS(TH)}	Gate Threshold Voltage	VDS=VGS,ID=-250μA	-1	-1.5	-2.5	V
R _{DS(ON)}	Drain-Source On-State Resistance (Note3)	VGS=-10V, ID=-20A	--	5.8	7.5	mΩ
		VGS=-4.5V, ID=-15A	--	9	12.6	mΩ
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated) (Note4)						
C _{iss}	Input Capacitance	VDS= -15V, VGS=0V, F=1MHz	--	3560	--	pF
C _{oss}	Output Capacitance		--	399	--	pF
C _{rss}	Reverse Transfer Capacitance		--	393	--	pF
Q _g	Total Gate Charge	VDS= -15V, ID= -20A, VGS= -10V	--	35	--	nC
Q _{gs}	Gate-Source Charge		--	6.2	--	nC
Q _{gd}	Gate-Drain Charge		--	9.2	--	nC
Switching Characteristics (Note4)						
t _{d(on)}	Turn-on Delay Time	VDD=-15V, ID=-30A, RG=2.5Ω, VGS=-10V	--	15	--	nS
t _r	Turn-on Rise Time		--	12	--	nS
t _{d(off)}	Turn-off Delay Time		--	50	--	nS
t _f	Turn-off Fall Time		--	28	--	nS
Source- Drain Diode Characteristics@ TJ = 25°C (unless otherwise stated)						
V _{SD}	Forward on voltage	IS=-30A,VGS=0V	--	--	-1.2	V

Note:

- Limited by TJmax, starting TJ = 25° C, RG = 25Ω, VD = -15V, VGS = -10V. Part not recommended for use above this value.
- Repetitive Rating: Pulse width limited by maximum junction temperature.
- Pulse Test: pulse width ≤ 300 us, duty cycle ≤ 2%.
- Guaranteed by design, not subject to production testing.

**-30V/-60A P-Channel Advanced Power MOSFET****Typical Characteristics**Figure1: T_J Junction Temperature (°C)Figure2: I_D Drain Current (A)Figure3: T_J Junction Temperature (°C)Figure4: V_{DS} Drain-Source Voltage (V)Figure5: V_{DS} Drain-Source Voltage (V)Figure6: Q_g Gate Charge (nC)



-30V/-60A P-Channel Advanced Power MOSFET




Figure7: Vsd Source-Drain Voltage (V)




Figure8: -Vgs Gate-Source Voltage (V)




Figure9: Vds Drain -Source Voltage (V)








Figure10: Square Wave Pulse Duration (sec)

**-30V/-60A P-Channel Advanced Power MOSFET****Test Circuit and Waveform:****Figure A Gate Charge Test Circuit & Waveforms****Figure B Switching Test Circuit & Waveforms****Figure C Unclamped Inductive Switching Circuit & Waveforms**

**-30V/-60A P-Channel Advanced Power MOSFET****TO-252 Package Outline Dimensions (Units: mm)**

COMMON DIMENSIONS (UNITS OF MEASURE IS mm)			
	MIN	NORMAL	MAX
A1	0.000	0.100	0.150
A2	2.200	2.300	2.400
A3	1.020	1.070	1.120
b	0.710	0.760	0.810
c	0.460	0.508	0.550
D	6.500	6.600	6.700
D1	5.330REF		
D2	4.830REF		
E	9.900	10.100	10.300
E1	6.000	6.100	6.200
E2	5.600REF		
e	2.286TYPE		
L	1.400	1.550	1.700
L2	1.10REF		
L3	0.80REF		
L4	1.80REF		
θ	$0 \sim 8^{\circ}$		
$\theta 1$	7° TYPE		
$\theta 2$	10° TYPE		
$\theta 3$	10° TYPE		