


Three-terminal positive voltage regulator

SOT-89-3L

1. OUT

2. GND



Marking: 78L12

特征 Features

- Maximum output current I_{OM} : 0.1A
- Output voltage V_o : 12V
- Continuous total dissipation P_D : 0.6W ($T_a=25^\circ\text{C}$)

机械数据 Mechanical Data

- SOT-89-3L Small Outline Plastic Package
- Epoxy UL: 94V-0
- Mounting Position: Any

Absolute Maximum Ratings (Operating temperature Range applies unless otherwise specified.)

Parameters	Symbol	Value	Unit
Input Voltage	V_i	35	V
Operating Junction Temperature Range	T_{OPR}	-25-+125	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	-65-+150	$^\circ\text{C}$
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	166.7	$^\circ\text{C/W}$


Electrical Characteristics at Specified Virtual Junction Temperature

($V_i=19\text{V}$, $I_o=40\text{mA}$, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$, unless otherwise specified).







Parameter	Symbols	Test Condition	Limits			Unit
			Min	Typ	Max	
Output Voltage	V_o	25°C	11.5	12	12.5	V
		$14\text{V} \leq V_i \leq 27\text{V}, I_o=1\text{mA} \sim 40\text{mA}$	11.4	12	12.6	V
		$I_o=1\text{mA} \sim 70\text{mA}$	11.4	12	12.6	V
Load Regulation	ΔV_o	$I_o=1\text{mA} \sim 100\text{mA}$		22	100	mV
		$I_o=1\text{mA} \sim 40\text{mA}$		13	50	mV
Line Regulation	ΔV_o	$14.5\text{V} \leq V_i \leq 27\text{V}$		55	250	mV
		$16\text{V} \leq V_i \leq 27\text{V}$		49	200	mV
Quiescent Current	I_q	25°C		4.3	6.5	mA
Quiescent Current Change	ΔI_q	$16\text{V} \leq V_i \leq 27\text{V}$			1.5	mA
	ΔI_q	$1\text{mA} \leq I_o \leq 40\text{mA}$			0.1	mA
Output Noise Voltage	V_N	$10\text{Hz} \leq f \leq 100\text{KHz}$		70		$\mu\text{V}/V_o$
Ripple Rejection	RR	$15\text{V} \leq V_i \leq 25\text{V}, f=120\text{Hz}$	37	42		dB
Dropout Voltage	V_d	25°C		1.7		V

* Pulse test.


TYPICAL APPLICATION



Note: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.

Typical characteristics



SOT-89-3L PACKAGE OUTLINE Plastic surface mounted package



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

Precautions: PCB Design

Recommended land dimensions for SOT-89-3L diode. Electrode patterns for PCBs



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

NOTICE

The information presented in this document is for reference only. Involving product optimization and productivity improvement, ChipNobo reserves the right to adjust product indicators and upgrade some technical parameters. ChipNobo is entitled to be exempted from liability for any delay or non-delivery of the information disclosure process that occurs.

本文件中提供的信息仅供参考。涉及产品优化和生产效率改善，ChipNobo 有权调整产品指标和部分技术参数的升级，所出现信息披露过程存在延后或者不能送达的情形，ChipNobo 有获免责权。

The product listed herein is designed to be used with residential and commercial equipment, and do not support sensitive items and specialized equipment in areas where sanctions do exist. ChipNobo Co., Ltd or anyone on its behalf, assumes no responsibility or liability for any damages resulting from improper use.

此处列出的产品旨在民用和商业设备上使用，不支持确有制裁地区的敏感项目和特殊设备，ChipNobo 有限公司或其代表，对因不当使用而造成的任何损害不承担任何责任。

For additional information, please visit our website <http://www.chipnobo.com>, or consult your nearest Chipnobo sales office for further assistance.

欲了解更多信息，请访问我们的网站 <http://www.chipnobo.com>，或咨询离您最近的 Chipnobo 销售办事处以获得进一步帮助。