




TVS Diodes Axial Leaded - 6kA > KB series

Descriptions

The KB series of high power TVS diode is specially designed for meeting severe surge test environment of both AC and DC line protection applications.

The KB features a very fast response and ultra low clamping characteristics as compared to MOVs (Metal Oxide Varistors). These KB components can be connected in series and / or parallel to create a very high surge current protection solution.



Maximum Ratings and Thermal Characteristics


(TA=25 C unless otherwise noted)

Parameter	Symbol	Value	Unit
Operating Storage Temperature Range	T _{STG}	-55 to 125	°C
Operating Junction Temperature Range	T _J	-55 to 125	°C
Surge Current Rating (tp=8/20μs)	I _{PP}	6	kA

Features

- Axial terminals
- High current & Excellent clamping capability.
- Glass passivated junction chip.
- Bi-directional.
- Low slope resistance.
- Hazardous Substances Free Compliant.
- RoHS compliant.
- High Temperature wave soldering: 265°C/10 seconds at terminals.
- Epoxy Coating.

Product Dimensions



Dimensions	Inches	Millimeters
A	0.95±0.04	24.15±1.0
B	0.095±0.024	2.4±0.60
C	0.236Min	6.00Min
D	0.630 Max	13.0 Max
E	0.050±0.002	1.28±0.05
F	0.630 Max	13.0 Max
G-030C	0.236Max	6.0Max
G-058C/C66C/076C	0.315Max	8.0Max
G-170C/190C/240C	0.551Max	14Max
G-380C/430C	0.708Max	18Max
L1=L2 tolerance±1.2mm		




Electrical Characteristics (TA=25°C unless otherwise noted)


Part Number	Reverse Stand-Off Voltage		Breakdown Voltage	Test Current	Current Rating	Maximum Clamping Voltage	Reverse Leakage
	V _{AC} (V)	V _{DC} (V)	Min. V _{BR} @ I _T (V)	I _T (mA)	I _{PP} @ 8/20μs (kA)	V _C @ I _{PP} (V)	I _R @ V _{DC} (μA)
KB-030C	21	30	33	10	6	100	2
KB-042C	30	42	47	10	6	105	2
KB-058C	40	58	64	10	6	110	2
KB-066C	45	66	70	10	6	120	2
KB-076C	54	76	85	10	6	140	2
KB-170C	130	170	180	10	6	260	2
KB-190C	145	190	200	10	6	290	2
KB-240C	180	240	250	10	6	340	2
KB-380C	275	380	401	10	6	520	2
KB-430C	341	430	440	10	6	625	2

Wave Solder Profile

Non Lead-free Profile




Lead-free Profile







Peak Power Derating




Typical Peak Pulse Power Rating Curve




Pulse Waveform - 10/1000μs waveform




Pulse Waveform - 8/20μs waveform



Part Marking System



Part Number System



Order information

Device		Qualities
KB Series		56pcs/Box