


SOD-123

特征 Features

- 齐纳击穿阻抗低; Low Zener Impedance
- 最大功率耗散 500mW; Power Dissipation of 500mW
- 高稳定性和可靠性。High Stability and High Reliability

机械数据 Mechanical Data

- 封装: SOD-123 封装 SOD-123 Small Outline Plastic Package
- 极性: 色环端为负极 Polarity: Color band denotes cathode end
- 环氧树脂 UL 易燃等级 Epoxy UL: 94V-0
- 安装位置: 任意 Mounting Position: Any

极限值和温度特性(TA = 25°C 除非另有规定)

Maximum Ratings & Thermal Characteristics (Ratings at 25°C ambient temperature unless otherwise specified.)

参数 Parameters	符号 Symbol	数值 Value	单位 Unit
功率消耗 Power Dissipation	Pd	500 ¹⁾	mW
正向压降 Forward Voltage @IF=10mA	Vf	0.9 ²⁾	V
存储温度 Storage temperature range	Ts	-65-+150	°C

1) Device mounted on ceramic PCB: 7.6mm x 9.4mm x 0.87mm with pad areas 25mm²

2) Short duration test pulse used to minimize self-heating effect

3) f=1KHz



电特性 (TA = 25°C 除非另有规定)







Electrical Characteristics (Ratings at 25°C ambient temperature unless otherwise specified.)







Device	Marking	Zener Voltage Range				Maximum Zener Impedance			Maximum Reverse Current		Typical Temperature coefficient @ IZTC=mV/°C		Test Current IZTC
		Vz@Izt			Izt	Zzt @Izt	Zzk @Izk	Izk	IR	VR	Min	Max	
		Nom(V)	Min(V)	Max(V)	mA	Ω		mA	uA	V			
BZT52C2V4	WX	2.4	2.28	2.52	5	100	600	1.0	50	1.0	-3.5	0	5
BZT52C2V7	W1	2.7	2.57	2.84	5	100	600	1.0	20	1.0	-3.5	0	5
BZT52C3V0	W2	3.0	2.85	3.15	5	95	600	1.0	10	1.0	-3.5	0	5
BZT52C3V3	W3	3.3	3.14	3.47	5	95	600	1.0	5	1.0	-3.5	0	5
BZT52C3V6	W4	3.6	3.42	3.78	5	90	600	1.0	5	1.0	-3.5	0	5
BZT52C3V9	W5	3.9	3.71	4.10	5	90	600	1.0	3	1.0	-3.5	0	5
BZT52C4V3	W6	4.3	4.09	4.52	5	90	600	1.0	3	1.0	-3.5	0	5
BZT52C4V7	W7	4.7	4.47	4.94	5	80	500	1.0	3	2.0	-3.5	0.2	5
BZT52C5V1	W8	5.1	4.85	5.36	5	60	480	1.0	2	2.0	-2.7	1.2	5
BZT52C5V6	W9	5.6	5.32	5.88	5	40	400	1.0	1	2.0	-2.0	2.5	5
BZT52C6V2	WA	6.2	5.89	6.51	5	10	150	1.0	3	4.0	0.4	3.7	5
BZT52C6V8	WB	6.8	6.46	7.14	5	15	80	1.0	2	4.0	1.2	4.5	5
BZT52C7V5	WC	7.5	7.13	7.88	5	15	80	1.0	1	5.0	2.5	5.3	5
BZT52C8V2	WD	8.2	7.79	8.61	5	15	80	1.0	0.7	5.0	3.2	6.2	5
BZT52C9V1	WE	9.1	8.65	9.56	5	15	100	1.0	0.5	6.0	3.8	7.0	5
BZT52C10	WF	10	9.50	10.50	5	20	150	1.0	0.2	7.0	4.5	8.0	5
BZT52C11	WG	11	10.45	11.55	5	20	150	1.0	0.1	8.0	5.4	9.0	5
BZT52C12	WH	12	11.40	12.60	5	25	150	1.0	0.1	8.0	6.0	10.0	5
BZT52C13	WI	13	12.35	13.65	5	30	170	1.0	0.1	8.0	7.0	11.0	5




Device	Marking	Zener Voltage Range				Maximum Zener Impedance			Maximum Reverse Current		Typical Temperature coefficient @ $I_{ZTC}=mV/^{\circ}C$		Test Current I_{ZTC}
		$V_Z@I_{ZT}$			I_{ZT}	$Z_{ZT}@I_{ZT}$	$Z_{ZK}@I_{ZK}$	I_{ZK}	I_R	V_R			
		Nom(V)	Min(V)	Max(V)	mA	Ω		mA	μA	V	Min	Max	mA
BZT52C15	WJ	15	14.25	15.75	5	30	200	1.0	0.1	10.5	9.2	13.0	5
BZT52C16	WK	16	15.20	16.80	5	40	200	1.0	0.1	11.2	10.4	14.0	5
BZT52C18	WL	18	17.10	18.90	5	45	225	1.0	0.1	12.6	12.4	16.0	5
BZT52C20	WM	20	19.00	21.00	5	55	225	1.0	0.1	14.0	14.4	18.0	5
BZT52C22	WN	22	20.90	23.10	5	55	250	1.0	0.1	15.4	16.4	20.0	5
BZT52C24	WO	24	22.80	25.20	5	70	250	1.0	0.1	16.8	18.4	22.0	5
BZT52C27	WP	27	25.65	28.35	2	80	300	0.5	0.1	18.9	21.4	25.3	2
BZT52C30	WQ	30	28.50	31.50	2	80	300	0.5	0.1	21.0	24.4	29.4	2
BZT52C33	WR	33	31.35	34.65	2	80	325	0.5	0.1	23.1	27.4	33.4	2
BZT52C36	WS	36	34.20	37.80	2	90	350	0.5	0.1	25.2	30.4	37.4	2
BZT52C39	WT	39	37.05	40.95	2	130	350	0.5	0.1	27.3	33.4	41.2	2
BZT52C43	WU	43	40.85	45.15	2	100	700	1.0	0.1	32.0	10.0	12.0	5
BZT52C47	WV	47	44.65	49.35	2	100	750	1.0	0.1	35.0	10.0	12.0	5
BZT52C51	WW	51	48.45	53.55	2	100	750	1.0	0.1	38.0	10.0	12.0	5

Breakdown characteristics
at $T_J=\text{constant}$ (pulsed)



Forward characteristics

Admissible power dissipation versus ambient temperature

Pulse thermal resistance versus pulse duration

Dynamic resistance versus Zener current

Capacitance versus Zener voltage

Dynamic resistance versus Zener current


Dynamic resistance versus Zener current

Thermal differential resistance versus Zener voltage

Dynamic resistance versus Zener voltage

Temperature dependence of Zener voltage versus Zener voltage

Temperature dependence of Zener voltage versus Zener voltage

Change of Zener voltage versus junction temperature



Change of Zener voltage versus junction temperature

Change of Zener voltage from turn-on up to the point of thermal equilibrium versus Zener voltage

SOD-123 PACKAGE OUTLINE Plastic surface mounted package


SYMBOL	DIMENSIONS	
	MIN.	MAX.
A	1.050	1.250
A1	0.000	0.100
A2	1.050	1.150
b	0.450	0.650
c	0.080	0.150
D	1.500	1.700
E	2.600	2.800
E1	3.550	3.850
L	0.500REF	
L1	0.250	0.450
θ	0°	8°

焊盘设计参考

Precautions: PCB Design

Recommended land dimensions for SOD-123 diode. Electrode patterns for PCBs



中心距: 3.24
 脚 宽: 0.55
 焊盘宽: 1.00
 脚 长: 0.50
 焊盘长: 0.80

技术要求:

- 1, 塑封体尺寸: 2.70 X 1.60
- 2: 未注公差为: ± 0.05
- 3, 所有单位: mm

NOTICE

The information presented in this document is for reference only. Involving product optimization and productivity improvement, ChipNobo reserves the right to adjust product indicators and upgrade some technical parameters. ChipNobo is entitled to be exempted from liability for any delay or non-delivery of the information disclosure process that occurs.

本文件中提供的信息仅供参考。涉及产品优化和生产效率改善，ChipNobo 有权调整产品指标和部分技术参数的升级，所出现信息披露过程存在延后或者不能送达的情形，ChipNobo 有获免责权。

The product listed herein is designed to be used with residential and commercial equipment, and do not support sensitive items and specialized equipment in areas where sanctions do exist. ChipNobo Co., Ltd or anyone on its behalf, assumes no responsibility or liability for any damages resulting from improper use.

此处列出的产品旨在民用和商业设备上使用，不支持确有制裁地区的敏感项目和特殊设备，ChipNobo 有限公司或其代表，对因不当使用而造成的任何损害不承担任何责任。

For additional information, please visit our website <http://www.chipnobo.com>, or consult your nearest Chipnobo sales office for further assistance.

欲了解更多信息，请访问我们的网站 <http://www.chipnobo.com>，或咨询离您最近的 Chipnobo 销售办事处以获得进一步帮助。