






OPERATING TEMPERATURE: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$



RECOMMENDED PCB PATTERN DIM.


TOLERANCE : ± 0.05

FFC TYPE A PATTERN DIM.


TOLERANCE : ± 0.05

REV.	REVISIONS	CHK	DATE


CUSTOMER		 臺華達 TAICHUAN		深圳市臺華達科技有限公司 SHENZHENSHI THD TECHNOLOGY CO., LTD.	
GENERAL TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN: Kavin		PART NO. THD0425--xxCL-GF	
X.X X.XX X.XXX ANG.		CHECKED: 胡文		TITLE: 0.4PITCH FPC 2.55H	
±0.35 ±0.25 ±0.15		APPROVED: JLM		SMT TYPE CONNECTOR WITH LOOK	
±2				SHEET: 1/2	
				UNIT: mm	
				SCALE: 1:1	
				SIZE: A4	
				REV: A	



SECTION: A-A



SECTION: B-B



ABOUT 264 MM LONG


(前后各空格22PCS)

UNLOADED SECTION

ABOUT 264 MM LONG

(前后各空格2PCS)

UNLOADED SECTION



						G/M (kg)	N/M (kg)	NO. OF CONTACTS
8000 PCS	2000	4	34.20	68.40	72.0	/	/	120
						/	/	110
						/	/	100
10000 PCS	2000	5	26.20	52.40	56.0	/	/	90
						/	/	80
QUANTITY	PCS/ TAPE	REEL/ CARTRON	DIM C	DIM F	DIM W	G/M (kg)	N/M (kg)	NO. OF CONTACTS

CUSTOMER



SHENZHENSHI THD TECHNOLOGY CO., LTD.

GENERAL TOLERAN

DRAWN: **Kavin** 2019.12.26

PART NO. THD0425 0001 CE

UNLESS

2013.12.20

CHECKED:

IHD0425-xxCL-GT

OFFICIAL OF THE

胡文	2019.12.26
----	------------

TITLE: 0.4Pitch FPC 2.5mm

X.X ±0.35

APPROVED: _____
TMM
0000000000

0.471111 FC 2.30

XX.XX	±0.25
10.45	

JLM	2019.12.26
	SHEET.

UNIT.	SCALE.	SIZE.	REF.
SMT	TYPE	CONNECIOR	PA

0.97
V.V.V.

0.98
U.V.U.

SHEET: 1/1

UNIT:	SCALE:	SIZE:	RE:
mm	1:1	A4	

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57	58	59	60	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77	78	79	80	81	82	83	84	85	86	87	88	89	90	91	92	93	94	95	96	97	98	99	100
---	---	---	---	---	---	---	---	---	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	-----

6	1/1		
---	-----	---	---

mm	1:1	A4
0		

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE ± 0.2
2. CAMBER NOT TO EXCEED 1mm IN 100mm.
3. MATERIAL: TRANSPARENT PS T=0.40 $\pm$ 0.05.
4. AO AND BO MEASURED ON A PLANE 0.3mm ABOVE THE BOTTOM OF THE POCKET.
5. KO MEASURED FROM A PLANE ON THE INSIDE/BOTTOM OF THE POCKET TO THE TOP SURFACE OF THE CARRIER TAPE.
6. POCKET POSITION RELATIVE TO SPROCKET HOLE MEASURED AS TRUE POSITION OF POCKET, NOT POCKET HOLE.
7. CARRIER TAPES, COVER TAPES, REELS AND TAPED COMPONENTS MUST MEET THE REQUIREMENTS DEFINED PER EIA-481-B.
8. PEELING SPEED: 300 mm/min.
9. COMPONENT LOOD PER 15" REEL: 2000 PCS.
10. PEELING OFF FORCE OF TOP TAPE: 0.1N-1.3N(10g/f~130g/f)