



Ultra-Fast Recovery Diodes
Reverse Voltage-200to600v
Forward current-16A

Features

- Ultra-Fast Recoveryt chip
- Fast reverse recovery time
- Ideal for surface mounted applications
- Low power loss, high efficiency
- Plastic Case Material has UL Flammability

Mechanical Data

Package: TO-220AB,TO-220F,TO-263,TO-252



Terminals:Tin Plated leads, solderable per

Mil-STD-750 Method 2026


Polarity: As marked

Molding compound meets UL 94 V-0 flammability rating,


ROHS-compliant




TO-220AB



TO-220F



TO-263



TO-252

Maximum Ratings (Ta=25°C Unless otherwise

Type Number	SYMBOL	MUR 1620	MUR 1640	MUR 1660	Umit
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	200	400	600	V
Maximum RMS Voltage	V _{RMS}	140	280	420	V
Maximum DC Blocking Voltage	V _{DC}	200	400	600	V
Maximum Average Forward Rectified Current at TL = 100 °C	IO _(AV)	16.0			A
Peak Forward Surge Current 8.3ms Single half-sine-wave superimposed on rated load(JEDEC Method) on rated	IFSM	100.0			A
Forward Surge Current (Non-repetitive) @1ms, square wave, 1 cycle, Tj=25°C		200.0			A
Current squared time @1ms≤t8.3≤ms Tj=25°C, Rating of per diode	I ² t	41.5			A ² S
Maximum Forward Voltage at 8.0A DC	V _{FM}	1	1.3	1.7	V
Maximum Reverse Current TA = 25°C	IR	5			uA
at Rated DC Blocking Voltage TA = 100°C		200			
Reverse Recovery Time	Trr	35			ns
Typical Junction Capacitance	CJ	50			pF
Typical Thermal Resistance TO-220AB,TO-263 TO-220F	R _{QJc}	2.0 4.0			°C/W
Operating Junction Temperature Range	T _J	—55to+150			°C
Storage Temperature Range	T _{STG}	—55to+150			°C



FIG. 1 MAXIMUM AVERAGE FORWARD CURRENT DERATING




FIG. 2 TYPICAL FORWARD CHARACTERISTICS




FIG. 3 MAXIMUM NON-REPEITIVE SURGE CURRENT






FIG. 4 TYPICAL REVERSE CHARACTERISTICS (per element)





MARKING INFORMATION

TO-220AB/CT




 = Polar line

 = Logo

***** = Date Code Marking

MUR***** = Marking Code

TO-220F/FCT




 = Polar line

 = Logo

***** = Date Code Marking

MUR***** = Marking Code

TO-263/CS
TO-252/DS



 = Polar line


 = Logo


***** = Date Code Marking


MUR***** = Marking Code



Package Outline Dimensions millimeters

T0-220AB/CT						
	DIM	INCHES		MM		NOTE
		min	max	min	max	
	A	—	0.41	—	10.30	
	B	0.33	0.34	8.30	8.70	
	C	0.18	0.19	4.50	4.90	
	D	0.57	0.60	14.60	15.20	
	E	0.53	0.56	13.50	14.10	
	a	0.10	0.10	2.45	2.65	
	b	—	0.16	—	4.10	
	c	0.03	0.04	0.72	0.92	
	d	0.01	0.02	0.30	0.50	
	e	—	0.15	—	3.80	Ø
	f	0.05	0.06	1.20	1.40	

T0-220F/FCT						
	DIM	INCHES		MM		NOTE
		min	max	min	max	
	A	—	0.41	—	10.30	
	B	0.61	0.64	15.60	16.20	
	C	0.18	0.19	4.50	4.90	
	D	0.26	0.28	6.60	7.00	
	E	0.50	0.53	12.80	13.40	
	a	0.10	0.10	2.45	2.65	
	b	—	0.16	—	4.10	
	c	0.03	0.04	0.72	0.92	
	d	0.02	0.02	0.40	0.60	
	e	—	0.15	—	3.80	Ø
	f	0.09	0.11	2.40	2.80	

T0-263/CS						
	DIM	INCHES		MM		NOTE
		min	max	min	max	
	A	—	0.41	—	10.30	
	B	0.33	0.34	8.30	8.70	
	C	0.18	0.19	4.50	4.90	
	D	0.38	0.39	9.60	10.00	
	E	0.21	0.22	5.30	5.70	
	a	0.10	0.10	2.45	2.65	
	b	—	0.16	—	4.10	
	c	0.03	0.04	0.72	0.92	
	d	0.01	0.02	0.30	0.50	
	e	0.05	0.06	1.20	1.40	



T0-252DS					
DIM	INCHES		MM		NOTE
	min	max	min	max	
A	0.25	0.27	6.3	6.9	
B	0.23	0.25	5.8	6.4	
C	0.08	0.10	2.1	2.5	
D	0.35	0.43	9.0	11.0	
E	0.21	0.22	5.3	5.5	
a	0.08	0.10	2.1	2.5	
b	0.06	0.06	1.4	1.6	
c	0.02	0.03	0.6	0.8	
d	0.02	0.02	0.4	0.6	
e	0.02	0.02	0.4	0.6	

Important Statements and disclaimers.

Do not copy or modify file information without permission.

Xumao Micro reserves the right to modify this document and its products.

Specifications are available without prior notice. Customer shall obtain and confirm the latest product information and specifications prior to final design, purchase or use.

Xumao Micro does not assume any implied warranties, including warranties of fitness for special purposes, non-infringement and merchantability.

The products shown here are not designed and licensed for demanding equipment at a level of reliability or for human life and any life-saving related applications or life-sustaining, such as medical devices, transportation equipment, aerospace machinery, and so on. Customers who use or sell these products for such applications do so at their own risk.

As Xumao Micro uses batch number as tracking benchmark, please provide batch number for tracking in case of exception.