

MSKSEMI 美森科

SEMICONDUCTOR



ESD



TVS



TSS



MOV



GDT



PLED


MSVB130T1G

Product specification

FEATURES

- Guardring for Stress Protection
- Low Forward Voltage
- 125°C Operating Junction Temperature
- Epoxy Meets UL 94 V-0 @ 0.125 in
- Package Designed for Optimal Automated Board Assembly
- ESD Ratings: Machine Model, C;
Human Body Model, 3
- We declare that the material of product compliance with
- RoHS requirements and Halogen Free.

Reference News

SOD-123	PIN ASSIGNMENT	MARKING
		

MAXIMUM RATINGS(Ta = 25°C)

Parameter	Symbol	Limits	Unit
Maximum repetitive peak reverse voltage	VRRM	30	V
Working Peak Reverse Voltage	VRWM		
Maximum DC blocking voltage	VR		
Average Rectified Forward Current (Rated VR) TL = 65°C	IF(AV)	1	A
Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions, Halfwave, Single Phase, 60 Hz)	IFSM	5.5	A
Thermal resistance (Note 1)	RθJA	230	°C/W
	RθJL	108	
Operating junction and storage temperature range	TJ	-65 ~ +125	°C
Voltage Rate of Change (Rated VR)	dv/dt	1000	V/μs




1. FR-4 or FR-5 = 3.5 × 1.5 inches using a 1 inch Cu pad

ELECTRICAL CHARACTERISTICS (Ta= 25℃)


Characteristic	Symbol	Min	Typ.	Max	Unit
Reverse Breakdown Voltage (IR=500μA)	VBR	30	-	-	V
Maximum instantaneous forward Voltage(Note 2) (IF = 0.1 A, TJ = 25℃)	VF	-	-	0.35	V
(IF = 0.7 A, TJ = 25℃)		-	-	0.45	
(IF = 1.0 A, TJ = 25℃)		-	0.47	-	
Maximum Instantaneous Reverse Current (Note 2) (VR=5V)	IR	-	-	10	μA
(VR=30V)		-	-	60	

2. Pulse Test: Pulse Width = 300 μs, Duty Cycle ≤ 2%.

ELECTRICAL CHARACTERISTICS CURVES




PACKAGE MECHANICAL DATA



Symbol	Dimensions In Millimeter		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.450	0.650	0.018	0.026
c	0.080	0.150	0.003	0.006
D	1.500	1.700	0.059	0.067
E	2.600	2.800	0.102	0.110
E1	3.550	3.850	0.140	0.152
L	0.500 REF		0.020 REF	
L1	0.250	0.450	0.010	0.018
θ	0°	8°	0°	8°

Suggested Pad Layout



Note:
1.Controlling dlmension:in millimeters.
2.General tolerance:± 0.05mm.
3.The pad layout Is for reference purposes only.

REEL SPECIFICATION

P/N	PKG	QTY
MSVB130T1G	SOD-123	3000

Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specification of any and all MSKSEMI Semiconductor products described or contained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringement of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.