









REV.	ECN NO OR DESCRIPTION	REVISED	DATE



NOTE:

1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERAL PLASTIC, UL 94V-0..
CONTACTS: COPPER ALLOY.
BORAD LOCK: COPPER ALLOY.
2. FINISH:
CONTACTS: GOLD FALSH PLATED ON CONTACT AREA, [100μ"] MIN..
BRIGHT-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT
UNDERPLATED [50μ"] MIN.. NICKEL.
BORAD LOCK: [100μ"] MIN. TIN OVER[50μ"]MIN. NICKEL PLATED.



SATA-007-M07XXBX-A

PLATING:
S1-[1μ"]GOLD CONTACT AREA
[100μ"]TIN SOLDER AREA
S2-[5μ"]GOLD CONTACT AREA
[100μ"]TIN SOLDER AREA

PACKING:
R-TAPE REEL
Y-TRAY
T-TUBE

HOUSING COLOR:
B-BLACK

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	SATA 7PIN 三面包90度DIP SMT		
X :±0.25	X :±2°	DWN	xiong	PART NO. SATA-007-M07S1BY-A	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					